Ringless Meter Socket Load Centers


These new models meet the latest requirements from the Florida Meter Group and other utilities that specify UL as their main requirement. They retain the features of prior models but offer ringless sockets and a few other improvements.



Key Product Changes

- Ringless meter cover
- Revised catalog number and ground labels
- · Latches and Hasps changed to Stainless
- Mounting bosses moved toward corners of enclosure
- 9/32" ground wire hole K/O in bottom
- Single latch centrally located hasp on Meter cover







Ringless Cat. No. (New)	UPC	Ring Type (Existing Cat. No.)
TSMR415CSFLFMG	78316441512	TSMF415CSFL
TSMR420CSFLFMG	78316441513	TSMF420CSFL
TSMR815CSFLFMG	78316441515	TSMF815CSFL
TSMR820CSFLFMG	78316441516	TSMF820CSFL
TSMR2020CSCUFMG	78316441517	N/A




Wiring Diagrams

TSMR415CSFLFMG, TSMR815CSFLFMG, TSMR420CSFLFMG TSMR820CSFLFMG TSMR2020CSCUFMG

Dunglan Cambal	Breaker Fill				
Breaker Symbol	1" THQL	1/2" THQP			
	1	-			
	1	2			

Tannain at Comphai	Wire Range (AWG/kcmil)				
Terminal Symbol	Cu	Al			
0	14-8	12-8			
•	14-4	12-4			
А	6-2	6-2			
В	14-1/0	12-1/0			
С	6-2/0	6-2/0			
D	1-300	2/0-300			
E	1-300	1-300			
F	6-1	6-1			
G	6-3	6-3			

Knockouts



Dimensions (in inches)

Box No.	Width	Width Height	
R36	14	28 1/2	4 1/2
R37	14	31 3/4	4 1/2

Symbol	Е	G	CC	EE	GG
	-	1/2	1/2	1/2	-
	3/4	3/4	3/4	3/4	-
	-	1	1	1	-
Conduit	-	-	1 1/4	1 1/4	1 1/4
Size In Inches	-	-	1 1/2	1 1/2	1 1/2
	-	-	2	2	2
	-	-	-	2 1/2	2 1/2
	-	-	-	-	3

Main Ampere Rating	1-Pole 1" Spaces	2-Pole 1" Spaces	1-Pole 1/2" Spaces	2-Pole, 1/2" Spaces	Total 1-Pole Spaces	Enclosure Type	Front Type	Bypass Type	UL Incoming	Agency Cert.	Product Number	List Price GO-137B
150	4	2	8	3	8	Outdoor (NEMA 3R)	Surface	None	OH/UG	UL FMG	TSMR415CSFLFMG	\$880.00
200	4	2	8	3	8	Outdoor (NEMA 3R)	Surface	None	OH/UG	UL FMG	TSMR420CSFLFMG	\$880.00
150	8	4	16	6	16	Outdoor (NEMA 3R)	Surface	None	OH/UG	UL FMG	TSMR815CSFLFMG	\$930.00
200	8	4	16	6	16	Outdoor (NEMA 3R)	Surface	None	OH/UG	UL FMG	TSMR820CSFLFMG	\$930.00
200	20	4	40	18	40	Outdoor (NEMA 3R)	Surface	None	OH/UG	UL FMG	TSMR2020CSCUFMG	\$1355.00

Product Number	Box Number	Unit Width	Unit Height	Depth	Factory Inst. Svcs Disc	Main Wire Size	Equipment Ground Kit
TSMR415CSFLFMG	R36A	14	28-1/2	4 1/2	THQMV	6-350	TGL2 Included
TSMR420CSFLFMG	R36A	14	28-1/2	4 1/2	THQMV	6-350	TGL2 Included
TSMR815CSFLFMG	R37A	14	31-3/4	4 1/2	THQMV	6-350	TGK24 Included
TSMR820CSFLFMG	R37A	14	31-3/4	4 1/2	THQMV	6-350	TGK24 Included
TSMR2020CSCUFMG	R40*	14	34-1/2	4 1/2	THQMV	6-350	TGK42 Included

^{*}Knock outs are the same as R36A.

GE

Industrial Solutions

41 Woodford Avenue Plainville, CT 06062 www.geindustrial.com

© 2012 General Electric Company



