




**Left Side View**



**Front View Interior**



**Front View Exterior**




**Notes**

1. PAINT: GRAY
2. FABRICATED FROM 16 GAUGE G90 GALVANIZED STEEL
3. UNIT RATING:  
20 AMP CONTINUOUS, 600 VAC, 3 PHASE, 4 WIRE
4. WIRED PER DECO SPECIFICATIONS WITH CONTINUOUS LOOP NEUTRAL WIRING.
5. UNIT IS SUPPLIED WITH TEMPORARY CARDBOARD METER OPENING COVER.
6. MIDWEST LABEL ATTACHED TO THE END OF THE CARTON.
7. MIDWEST LOGO STAMPED ON LOWER LEFT HAND CORNER OF FRONT.
8. SAFETY LABEL IS LOCATED ON THE LOWER RIGHT-HAND CORNER OF THE FRONT
9. EACH TEST SWITCH CONNECTION STUD IS SUPPLIED WITH:
  - (1) 10-32 X 1/2 WAF X 5/16 THK HEX FLANGE NUT.
  - (1) 10-32 X 1/2 WAF X 3/16 THK HEX NUT.
  - (2) 1/2" SQ WASHERS WITH 7/32" HOLE.

**Bottom View**



		
METER SKT-(1) 20A 600V G90 N3R 13-TERM SOLID TOP 10-POLE BOTTOM FEED DECO TEST SWITCH		
<b>CAT NO</b>	<b>DWG DATE</b>	<b>REV #</b>
1007003CMEP	04/15/2016	02