

FOR THXXXXJR CATALOGS ONLY

WINDOW FOR THXXXXJW CATALOGS




FIG. 1





FIG. 2



DIMENSION TABLE

GCAT NO.	FIG.	A	B	C	D	E	F	G	H	I
THN2263JDC	1	25.36	13.42	14.04	13.12	25.08	26.28	10.50	10.12	-
TH3223J/TH4323J/THN3363J/TH3363J/ THN3363JCL/TH2263JDC	1	25.36	13.42	14.04	13.14	25.08	26.28	10.50	10.12	-
THN3363JW/TH3363JW	2	25.36	13.42	14.04	13.14	25.08	26.28	10.50	10.12	-
TH3363JR	1	25.36	13.42	14.04	13.14	25.08	26.28	10.50	10.12	13.59
TH3364J/TH4324J/TH3224J/THN3364J	1	35.14	14.45	15.07	14.14	34.83	36.06	11.50	10.12	-
TH3224JW/TH4324JW	2	35.14	14.45	15.07	14.14	34.83	36.06	11.50	10.12	-
THN3364JW/TH3364JW	2	35.14	14.45	15.07	14.14	34.83	36.06	11.50	10.12	-
TH3364JR	1	35.14	14.45	15.07	14.14	34.83	36.06	11.50	10.12	14.59
TH3223JW/TH4323JW	2	25.36	13.42	14.04	13.12	25.08	26.28	10.50	10.12	-

NOTE:
1. ALL DIMENSIONS ARE IN INCHES.
2. ALL DIMENSIONS HAVE ± 0.125 TOLERANCE.



Industrial Solutions

by ABB

OUTLINE DRAWING-HEAVY DUTY 100 & 200A
NEMA-12 & 12/3R, WITH & WITHOUT VIEWING WINDOW

THIRD ANGLE	SHEET#
	1 of 1

DWG NO.	DATE	REV
10103091SH120	10/19	06