



DIMENSION TABLE

GCAT NO.	FIG.	A	B	C	D	E	G	H	I
TH2263MDC/THN2263MDC	1	25.35	13.41	15.25	13.13	25.07	25.60	10.50	10.12
TH3363M/THN3363M/TH3323M/TH2223M	1	25.35	13.41	15.25	13.13	25.07	25.60	10.50	10.12
TH3364M/THN3364M/TH3324M/TH2224M	2	35.13	14.44	16.28	14.13	34.82	35.38	11.50	10.12
TH2223MSS/TH3323MSS/TH3363MSS	2	25.35	13.41	15.25	13.28	25.22	25.60	10.50	10.36
THN3363MSS	2	25.35	13.41	15.25	13.28	25.22	25.60	10.50	10.36
TH3324MSS/TH2224MSS	2	35.13	14.44	16.28	14.28	34.97	35.38	11.50	10.36
TH3364MSS/THN3364MSS	2	35.13	14.44	16.28	14.28	34.97	35.38	11.50	10.36

NOTE:

1. ALL DIMENSIONS ARE IN INCHES.
2. ALL DIMENSIONS HAVE ± 0.125 TOLERANCE.
3. ADDITIONAL BRACKET FOR 200A CATALOGS.



Industrial Solutions

by **ABB**

OUTLINE DRAWING-MILL DUTY SAFETY SWITCH
100 & 200A, NEMA - TYPE 12 ENCLOSURE

THIRD ANGLE	SHEET#
	1 of 1

DWG NO.	DATE	REV
10103091SH128	08/19	06