


Note : All Dimensions have ±0.125 Tolerance



LETTER	DESCRIPTION	QTY
A	1 1/2 x 2 x 2 1/2 KO	2
B	3/4 x 1 x 1 1/4 x 1 1/2 KO	3
C	1/2 x 3/4 x 1 KO	1
D	1/2 x 3/4 KO	11
E	9/32 KO	2
F	2 1/2 x 3 x 3 1/2 x 4 KO	1
G	1/2 x 3/4 x 1 1/4 x 1 1/2 x 2 KO	2
H	1/2 x 3/4 x 1 1/4 x 1 1/2 x 2 x 2 1/2 KO	2

CAT NO.	MODEL
TM2430RMRS	1
TMH2430RMRS	1
TMH2440RMRS	2
TMH2440RMS	2
TM2440RMS	1
TM2440RM	1
TM2440RMRS	1
TM2440RMR	1
TM2432RMS	1
TMH2432RMS	1

imagination at work

OUTLINE DRAWING
400 A METER SOCKET LOAD CENTER

DWG NO.	DATE	REV
10103091SH36	07/03/2009	01