


KNOCKOUT DIAGRAM

| DIMENSION TABLE |       |        |        |
|-----------------|-------|--------|--------|
| CATALOG#        | MODEL | A      | B      |
| TLC4240F        | 1     | 46.63" | 17.38" |
| TLC4240S        | 1     | 45.25" | 16.23" |
| TLC42440F       | 1     | 46.63" | 17.38" |
| TLC42440S       | 1     | 45.25" | 16.23" |

| KNOCKOUT TABLE |                                      |      |
|----------------|--------------------------------------|------|
| SYM.           | SIZE                                 | QTY. |
| A              | 1/2 KO                               | 98   |
| B              | 9/32 KO                              | 6    |
| C              | 3/4 X 1 X 1 1/4 KO                   | 4    |
| D              | 3/4 X 1 X 1 1/4 X 2 X 2 1/2 KO       | 4    |
| E              | 3/8 X 1/2 X 3/4 KO                   | 4    |
| F              | 3/4 X 1 X 1 1/4 X 3 1/2 KO           | 2    |
| G              | 1/2 X 3/4 X 1 X 1 1/2 X 2 X 2 1/2 KO | 12   |

NOTE: ALL KO LOCATING DIMENSIONS ARE INSIDE OF BOX.

ALL DIMENSIONS HAVE +/- .125 TOLERANCE

 **imagination at work**

OUTLINE DRAWING  
CSA INDOOR LOAD CENTER

|               |          |     |
|---------------|----------|-----|
| DWG NO.       | DATE     | REV |
| 10103091SH159 | 01/08/10 | 01  |