



SYMBOL	SIZE	QTY.
A	9/32 KO	4
B	1/2 KO	28
C	1/2 X 3/4 KO	15
D	1/2 X 3/4 X 1 KO	1
E	1/2 X 3/4 X 1 X 1 1/4 KO	5
F	1 X 1 1/4 X 1 1/2 X 2 KO	2
G	1 X 1 1/2 X 2 X 2 1/2 KO	5
H	1 X 1 1/4 X 1 1/2 X 2 X 2 1/2 KO	2
I	.219 X .08 OBLONG KO	4

CAT. NO.	MODEL
TM3210CCU	1
TM30412C	3
TM24415C	3
TM30415C	3
TM3215CCU	6
TM3215C42	6
TM24420C	2
TM3220CCU	7
TM3220C42	7
TM24415CB	3
TM30412CB	3
TM30415CB	3
TLM3220CCU	7
TL30420C	2
TM24420CB	2
TL30420CX2	2
TL30420C	1
TM3220CCPL13	7
TM3220CCU2K	7

CAT. NO.	MODEL
TM24415CBX2	2
TM24415CX2LB	2
TM24415CX2	2
TL30420CEIL	2
TLM3220C42	7
TLM3220CCU1K	7
TLM3220CCUW	7
TM1ST30412C	2
TM24420CX2	2
TM2ST30412C	2
TM30410CX2	1
TM30412CX2	1
TM30415CX2LB	2
TM30415CX2	2
TM3210CCUP	1
TM3215CCU1K	6
TM3220CCU4K	7
TM3220CCU5KW	7
TM24410CX2	1

KNOCKOUT DIAGRAM

NOTE: ALL KO LOCATING DIMENSIONS ARE INSIDE OF BOX.

ALL DIMENSIONS HAVE +/- .125 TOLERANCE



OUTLINE DRAWING
INDOOR LOAD CENTER

DWG NO.	DATE	REV
10103091SH21	06/11/09	02