




**GE PROPRIETARY AND CONFIDENTIAL INFORMATION**  
 This document is the property of General Electric Company ("GE") and contains proprietary information of GE. This document is loaned on the express condition that neither it nor the information contained therein shall be disclosed to others without the express written consent of GE Industrial Systems, and that the information shall be used by the recipient only as approved expressly by GE Industrial Systems. This document shall be returned to GE upon its request. This document may be subject to certain restrictions under U.S. export control laws and regulations.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
1	R1102469	YY 02/18/11	AJ

METRIC



ISOMETRIC VIEW



NOTE A

PV4

ITEM	QTY	MODEL NAME	DESCRIPTION
5	24	N210P29B6	NUT
4	24	N22P29048B6	SCREW, HEX HEAD CAP
3	24	N405P45B6	LOCK WASHER
2	48	N402P73B6	WASHER
1	2	10100276PI	SHORTING LINK

BILL OF MATERIAL

TIGHTENING TORQUES	
FASTNER TYPE	TORQUE VALUE Nm
M12	80 Nm

FOR ADDITIONAL INFO REFER TO:		SIGNATURES		DATE
APPLIED PRACTICES	EDB	MODEL	JOE	03/01/11
DIMENSIONS ARE IN MILLIMETERS		DETAIL	YY	03/01/11
<b>UNLESS OTHERWISE SPECIFIED IN DRAWING</b>		CHECKED	RAGHAV	03/01/11
TOLERANCE ON:		ENGRG		
1 PL DECIMALS ± 0.3		MFG		
2 PL DECIMALS ± 0.13		QUALITY		
ANGLES ± 0.5		ISSUED		
FRACTIONS ±		DRIVING FILE:	10108126PV4	
FINISH		SOLID MODEL:	10108126G1	
◇ CRITICAL TO QUALITY CHARACTERISTIC				


**GE Consumer & Industrial** GENERAL ELECTRIC COMPANY

TITLE **TERMINAL KIT MOUNTING ASM FOR UL PV BREAKER 3000A**

SIZE DRAWING	REV
A3	1
SCALE: 1:10	REF. No.:

NOTE A: THIS POLE WILL NOT BE AVAILABLE FOR USE IN 3 POLEBREAKER VERSION.

Article or Material Must Conform to RoHS Procedure SI900000 Sec. 13  
 Part must conform to SI 900000 Sect. 4, Toxicity Procedure



METRIC