

APPROX TOTAL WEIGHT LBS [KG]
 PAINTED: 400 [181]

kVA RATING:
 K-FACTOR:
 PRI VOLTAGE:
 SEC VOLTAGE:
 FREQ (Hz):
 TEMP RISE:
 WINDING MATL:
 ES SHIELD:
 SOUND LVL (dB):

| KNOCKOUTS | |
|---------------------------|----------------|
| CONDUIT SIZE | TOTAL QUANTITY |
| 1" OR 2" [27 OR 53 MM] | 8 |


JOB NAME:
 SPEEDI PROP:

electrification.us.abb.com

CAD DRAWING: 303B923AAP025

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCH [MM]

THIRD ANGLE PROJECTION



SHEET 1 OF 1



Transformers

by ABB

DRY TYPE TRANSFORMER OUTLINE DRAWING
 TYPE QMS, 1-PHASE
 (ENCLOSED INDOOR/OUTDOOR UNIT)

CATALOG #

REV 4