



STYLE NO.	DUTY CYCLE kV	MCOV kVrms	CREEPAGE		LBS	KG	PH TO GRD.		PH TO PH		FIGURE
			IN	MM			IN	MM	IN	MM	
D0385A029ADE00	36	29.0	51.6	1311	14.0	6.4	16.85	428	17.20	437	1
D0385A029ADE00	36	29.0	51.6	1311	14.0	6.4	16.85	428	17.20	437	2
D0385A029ADE00	36	29.0	51.6	1311	14.0	6.4	16.85	428	17.20	437	3
D0385A031ADE00	39	31.5	51.6	1311	14.0	6.4	16.85	428	17.20	437	1
D0385A031ADE00	39	31.5	51.6	1311	14.0	6.4	16.85	428	17.20	437	2
D0385A031ADE00	39	31.5	51.6	1311	14.0	6.4	16.85	428	17.20	437	3



- E - CABLE TERMINAL WITH M12 STUD, 2 NUTS LOCKWASHER, FLAT WASHER AND TERMINAL CLAMP.
  - P - CABLE TERMINAL WITH INSULATING BRACKET, M12 STUD, 2 NUTS, LOCKWASHER, FLAT WASHER AND TERMINAL CLAMP.
  - 0 - CABLE TERMINAL WITH INSULATING BRACKET & DISCONNECTOR WITH M12 STUD, M10 NUT, LOCKWASHER, FLAT WASHER AND TERMINAL CLAMP.
- NAMEPLATE  
0 - STANDARD ANSI ONLY

**HORIZONTAL 3Ø INSTALLATION LAYOUT**



**FIGURE 1**

**FIGURE 2**

**FIGURE 3**

ALL DIMENSIONS IN INCH (MM) UNLESS NOTED  
DIMENSIONS ARE TO CENTER UNLESS NOTED  
DIMENSIONS TO CENTER UNLESS NOTED  
DIMENSIONS TO CENTER UNLESS NOTED

STANDARD POLIM-D ARRESTER 36 & 39kV OUTLINE	
ABB INC. Power Product Division 100 Distribution Circle, Ft. Peck, PA 15045	
SCALE	AS SHOWN
DATE	04/14/2014
BY	DKM
CHECKED	DKM
APPROVED	DKM
SHEET 1 OF 1	4F1006
REV	4

01	OCT. 10, 2006	UPDATED FIGURES 2 AND 3 WITH NEW INSULATING BRACKET (HAR200721)
02	AUGUST 12, 2008	FIGURE 2 DISCONNECTOR UPDATED HARDWARE
03	APRIL 14, 2014	FOR NEW DISCONNECTOR FROM MMS 21.9 WAS 25.66 REF FIGURE 2: 29.84 REF
04	OCTOBER 1, 2015	STYLE CHART: UPDATED "S" AND "T" VALUES HORIZONTAL ADDED TO 3Ø CALCULON
03	APRIL 14, 2014	39 kV STYLES ADDED TITLE UPDATED DKM
04	OCTOBER 1, 2015	

FOR TENDER PURPOSES ONLY