


DUAL DIMENSIONS INCHES (ESTIMATING ONLY)  
[MILLIMETERS]



NOTE : FOR 2 POLE SWITCH OMIT CENTER POLE

PART	SIZE	A	B	C	D	E	F	G	H
1	30 A	6.50 [165.1]	7.50 [190.5]	0.50 [12.7]	0.50 [12.7]	9.00 [228.6]	10.00 [250.4]	0.25 [6.4]	10.50 [266.7]
2	60-75-100 A	6.75 [171.5]	7.75 [196.8]	0.50 [12.7]	0.63 [16.0]	9.75 [247.7]	11.00 [279.4]	0.19 [4.8]	11.38 [289.1]
3	150 A	8.00 [203.2]	9.00 [228.6]	0.50 [12.7]	3.25 [82.5]	5.50 [139.7]	12.00 [304.8]	0.63 [16.0]	13.25 [336.6]
4	200 A	8.00 [203.2]	9.00 [228.6]	0.50 [12.7]	3.25 [82.5]	5.50 [139.7]	12.00 [304.8]	1.00 [25.4]	14.00 [355.6]
5	30 A COM. MOUNT	8.00 [203.2]	9.00 [228.6]	0.50 [12.7]	3.25 [82.5]	5.50 [139.7]	12.00 [304.8]	0.25 [6.4]	12.50 [317.5]
6	30 A RING TERM	6.50 [165.1]	7.50 [190.5]	0.50 [12.7]	0.50 [12.7]	9.00 [228.6]	10.00 [254.0]	0.31 [7.9]	10.63 [270.0]
7	60 A RING TERM	6.75 [171.5]	7.75 [196.8]	0.50 [12.7]	0.63 [16.0]	9.75 [247.7]	11.00 [279.4]	0.88 [22.2]	12.72 [323.1]
8	75 A RING TERM	6.75 [171.5]	7.75 [196.8]	0.50 [12.7]	0.63 [16.0]	9.75 [247.7]	11.00 [279.4]	0.97 [24.6]	12.91 [327.9]
9	100 A RING TERM	6.75 [171.5]	7.75 [196.8]	0.50 [12.7]	0.63 [16.0]	9.75 [247.7]	11.00 [279.4]	1.06 [26.9]	13.09 [332.5]
10	150 A RING TERM	8.00 [203.2]	9.00 [228.6]	0.50 [12.7]	3.25 [82.5]	5.50 [139.7]	12.00 [304.8]	1.50 [38.1]	15.00 [381.0]
11	200 A RING TERM	8.00 [203.2]	9.00 [228.6]	0.50 [12.7]	3.25 [82.5]	5.50 [139.7]	12.00 [304.8]	1.63 [41.4]	15.25 [387.4]



OUTLINE  
CR160MC LIGHTING CONTACTOR

AN #	THIRD ANGLE PROJECTION	SHEET #
09-9107		1 OF 1

DWG NO.	DATE	REV
55-172306	07/28/2009	5