



Transformer

by ABB




1M000000

Catalog Number 9T10A1094 **Type** QL


75.0 KVA 60 HZ 3 PH 4.9 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 415 VOLTS (LINE-LINE)
240 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1	505
2	494
3	480
4	468
5	457
6	443
7	432



COIL TAP ARRANGEMENT



NET WGT
561 LB
254.5 Kg
89149
UY74A

INSPECTION & FINAL TEST
NOG
N137!
091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

X3	H3	X2	H2	X1	H1
-	-	-	-	-	-

Note: X0 at the bottom

Outline: 303B111GEUY74A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X3 H3 X2 H2 X1 H1
X3 H3 X2 H2 X1 H1
X0



2M000000



3M000000