



Transformer

by ABB




1M000000

Catalog Number 9T10A1114 **Type** QL


75.0 KVA 60 HZ 3 PH 5.8 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 480 VOLTS (LINE-LINE)
SECONDARY (H) 575 VOLTS (LINE-LINE)

JUMPER CONNECTION	TAP	VOLTS
1	503	
2	493	
3	480	
4	469	
5	455	
6	445	
7	431	



COIL TAP ARRANGEMENT



NET WGT
561 LB
254.5 Kg
89158
UY74A

INSPECTION & FINAL TEST
NOG
N137!
091021



H3 X3 H2 X2 H1 X1
- - - - -
H3 X3 H2 X2 H1 X1
- - - - -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1
- - - - -
Note: standard

Outline: 303B111GEUY74A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

