



Transformer

by ABB




1M000000

Catalog Number 9T10A1123 **Type** QL


45.0 KVA 60 HZ 3 PH 3.3 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 480 VOLTS (LINE-LINE)
SECONDARY (H) 600 VOLTS (LINE-LINE)

JUMPER CONNECTION	TAP VOLTS
1	503
2	493
3	480
4	467
5	457
6	443
7	433



COIL TAP ARRANGEMENT



NET WGT
444 LB
201.4 Kg
88749
UX73A

INSPECTION & FINAL TEST
NOG
N137!
091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 X3 H2 X2 H1 X1 -

Note: standard

Outline: 303B111GEUXP73A

H3 X3 H2 X2 H1 X1 -

H3 X3 H2 X2 H1 X1 -

2M000000

3M000000