



# Transformer



\*1M000000\*


Catalog Number  
**9T10A1175G31**

Type **QL**


**112.5 KVA 60 HZ 3 PH 5.6 % IMP**

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 480 VOLTS (LINE-LINE)  
277 VOLTS (LINE-NEUTRAL)



### COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1-2	503
2-3	490
3-4	480
4-5	469
5-6	456
6-7	443
7-8	431

NET WGT  
830 LB  
376.5 Kg

60794  
DK75A

NOG  
040416

INSPECTION  
&  
FINAL TEST  
N615!



LISTED 769G

Assembled in Mexico

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

Outline:  
303B111GEDXP75A

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE**

X3 - X2 - X1 - -  
- H3 - H2 - H1

Note: X0 at the bottom

X1 - -  
X2 - H1  
X3 - H2 - H1  
X3 - X2 - X1 -  
H3 - H2 - H1  
X3 - X2 - X1 -  
H3 - H2 - H1  
X0



\*2M000000\*



\*3M000000\*