



# Transformer



\*1M000000\*

X4


Catalog Number

Type QL

9T10A1186

150.0 KVA 60 HZ 3 PH 4.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C



JUMPER CONNECTION	
TAP	VOLTS
1-2	503
2-3	492
3-4	480
4-5	469
5-6	457
6-7	446
7-8	434

NET WGT  
1030 LB  
467.2 Kg


60439  
DY76A

NOG  
022516

INSPECTION  
&  
FINAL TEST  
N609!

PRIMARY (H) 480 VOLTS (LINE-LINE)  
 SECONDARY (X) 240 VOLTS (LINE-LINE)  
 120 VOLTS (1 PH MIDTAP)

### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR

PRIMARY: 10 KV BIL

SECONDARY: 10 KV BIL

Outline:

303B111GEDYP76A

Assembled in Mexico

X3 - X2 - X1 - X4  
 - H3 - H2 - H1

Note: MID-TAP

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
 CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE

X4  
 - X1 - H1  
 - X2 - H2  
 - X3 - H3  
 - X1 - H1  
 - X2 - H2  
 - X3 - H3



\*2M000000\*



\*3M000000\*