



Transformer

by ABB




1M000000

Catalog Number **Type QL**
9T10A1194G02


75.0 KVA 60 HZ 3 PH 5.6 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 240 VOLTS (LINE-LINE)

JUMPER CONNECTION	TAP	VOLTS
1	505	
2	491	
3	480	
4	469	
5	455	
6	445	
7	431	



COIL TAP ARRANGEMENT



NET WGT	INSPECTION & FINAL TEST
561 LB	
254.5 Kg	NOG
89227	N137!
UY74A	091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X3 H3 X2 H2 X1 H1

Note: standard

Outline: 303B111GEUY74A

X3 H3 X2 H2 X1 H1

2M000000

3M000000