



Transformer

by ABB




1M000000

Catalog Number 9T10A1321 **Type** QL


15.0 KVA 60 HZ 3 PH 3.7 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)
SECONDARY (H) 240 VOLTS (LINE-LINE)
120 VOLTS (1 PH MIDTAP H1-H4)

JUMPER CONNECTION	TAP VOLTS
1	218
2	214
3	208
4	203
5	197
6	193
7	187



COIL TAP ARRANGEMENT



NET WGT 231 LB
INSPECTION & FINAL TEST 104.8 Kg
NOG 89243
N139! UX71A
092021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06
REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 X3 H2 X2 H1 X1 H4

Note: MID-TAP

Outline: 303B111GEUXP71A

H3	X3	H2	X2	H1	X1	H4
2M000000						
H3	X3	H2	X2	H1	X1	H4
3M000000						