



# Transformer



\*1M0000000\*

H4  
H1 X1  
H1 X1  
H2 X2  
H2 X2  
H3 X3  
H3 X3  
H4  
H4

Catalog Number

Type QL

9T10A1324

75.0 KVA 60 HZ 3 PH 5.7 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

JUMPER CONNECTION  
TAP VOLTS  
1-2 219  
2-3 212  
3-4 208  
4-5 201  
5-6 198

NET WGT  
561 LB  
254.5 Kg


60796  
LY74A

NOG  
040416

INSPECTION  
&  
FINAL TEST  
N615!

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 240 VOLTS (LINE-LINE)  
120 VOLTS (1 PH MDTAP)

### COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR

PRIMARY: 10 KV BIL

SECONDARY: 10 KV BIL

Outline:

303B111GEUY74A

Assembled in Mexico

H3 X3 H2 X2 H1 X1 H4

- - - - -

Note: MID-TAP

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE



\*2M0000000\*



\*3M0000000\*