



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10A1412 **Type** QL

30.0 KVA 60 HZ 3 PH 4.8 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 230 VOLTS (LINE-LINE)  
133 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1	218
2	214
3	208
4	202
5	198
6	192
7	186




**NET WGT**  
330 LB  
149.7 Kg  
89300  
UX72A

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



LISTED 769G

### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 X3 H2 X2 H1 X1 H0

Note: standard

Outline: 303B111GEUXP72A

H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-

\*2M000000\*

\*3M000000\*