



Transformer

by ABB



1M000000

Catalog Number 9T10A1592 **Type** QL


30.0 KVA 60 HZ 3 PH 5 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 240 VOLTS (LINE-LINE)
SECONDARY (X) 240 VOLTS (LINE-LINE)
139 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1	251
2	245
3	240
4	235
5	229
6	223
7	217



COIL TAP ARRANGEMENT



NET WGT
330 LB
149.7 Kg
89347
UX72A

INSPECTION & FINAL TEST
NOG
N139!
092021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X3 H3 X2 H2 X1 H1 X0

Note: standard

Outline: 303B111GEUXP72A

X3 H3 X2 H2 X1 H1 X0
X3 H3 X2 H2 X1 H1 X0
X3 H3 X2 H2 X1 H1 X0

