



Transformer

by ABB



1M000000

Catalog Number 9T10A2221 **Type** QL

15.0 KVA 60 HZ 3 PH 3.5 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 460 VOLTS (LINE-LINE)
SECONDARY (X) 220 VOLTS (LINE-LINE)
127 VOLTS (LINE-NEUTRAL)

| JUMPER CONNECTION | TAP VOLTS |
|-------------------|-----------|
| 1 | 483 |
| 2 | 472 |
| 3 | 460 |
| 4 | 449 |
| 5 | 436 |
| 6 | 425 |
| 7 | 415 |




NET WGT
231 LB
104.8 Kg
89412
UX71A

INSPECTION & FINAL TEST
NOG
N139!
092021



COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 X0

Note: standard

Outline: 303B111GEUXP71A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X0
X1 H1
X2 H2
X3 H3

