



Transformer

by ABB



1M000000

Catalog Number **Type** **QL**
9T10C1002G35

30.0 KVA 60 HZ 3 PH 3.7 % IMP
 40 C AMB. 115 C RISE 220 C SYSTEM IS-19C


PRIMARY (H) 480 VOLTS (LINE-LINE)
 SECONDARY (X) 208 VOLTS (LINE-LINE)
 120 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION

TAP	VOLTS
1	503
2	493
3	480
4	468
5	455
6	445
7	432



COIL TAP ARRANGMENT



NET WGT
 353 LB
 160.1 Kg
 89478
 UX72C

INSPECTION & FINAL TEST
 NOG
 N139!
 092021



X3	H3	X2	H2	X1	H1	X0
-	-	-	-	-	-	-
X3	H3	X2	H2	X1	H1	X0
-	-	-	-	-	-	-



2M000000



3M000000

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3	H3	X2	H2	X1	H1	X0
-	-	-	-	-	-	-

Note: standard

Outline: 303B111GEUXP72C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency