



Transformer

by ABB




1M000000

Catalog Number 9T10C1093G31 **Type** QL


45.0 KVA 60 HZ 3 PH 3.1 % IMP
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 415 VOLTS (LINE-LINE)
240 VOLTS (LINE-NEUTRAL)

| JUMPER CONNECTION TAP | VOLTS |
|-----------------------|-------|
| 1 | 505 |
| 2 | 494 |
| 3 | 480 |
| 4 | 468 |
| 5 | 457 |
| 6 | 443 |
| 7 | 432 |



COIL TAP ARRANGEMENT



NET WGT
480 LB
217.7 Kg
88864
UX73C

INSPECTION & FINAL TEST
NOG
N137!
091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 -

Note: X0 at the top

Outline: 303B111GEUXP73C


NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X3 H3 X2 H2 X1 H1 -
 X3 H3 X2 H2 X1 H1 -
 X3 H3 X2 H2 X1 H1 -



2M000000



3M000000

X0