



Transformer

—
by ABB



1M000000


Catalog Number **Type QL**
9T10C1179

500.0 KVA 60 HZ 3 PH 3 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


JUMPER CONNECTION

TAP	VOLTS
1-2	503
2-3	493
3-4	480
4-5	472
5-6	452

PRIMARY (H)	480 VOLTS (LINE-LINE)
SECONDARY (X)	480 VOLTS (LINE-LINE)
	277 VOLTS (LINE-NEUTRAL)



COIL TAP ARRANGEMENT



NET WGT	INSPECTION & FINAL TEST
3720 LB	
1687.4 Kg	NOG
89649	N137!
DX79C	091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1079G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

Outline: 303B112GEDXP79C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



2M000000



3M000000