



Transformer

by ABB





1M000000

Catalog Number 9T10C1195 **Type** QL

112.5 KVA 60 HZ 3 PH 5.7 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 240 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	503
2-3	491
3-4	480
4-5	467
5-6	457
6-7	446
7-8	434



NET WGT
790 LB
358.3 Kg
89683
DY75C

INSPECTION & FINAL TEST
NOG
N137!
091021



X3 - X2 - X1 - H3 - H2 - H1
X3 - X2 - X1 - H3 - H2 - H1

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

ASSEMBLED IN MEXICO

X3 - X2 - X1 - -
- H3 - H2 - H1
Note: standard

Outline: 303B11GEDYP75C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

