



# Transformer




\*1M000000\*

Catalog Number  
**9T10C1338G61**

Type **QL**

**300.0 KVA 60 HZ 3 PH 2.7 % IMP**

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C



JUMPER CONNECTION	
TAP	VOLTS
1-2	226
2-3	216
3-4	208
4-5	198
5-6	188

NET WGT  
3720 LB  
1687.4 Kg


60507  
DK79C

NOG  
030216

INSPECTION  
&  
FINAL TEST  
**N610!**

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 480 VOLTS (LINE-LINE)

### COIL TAP ARRANGEMENT



\*2M000000\*



\*3M000000\*

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1079G06

Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

Outline:  
303B112GEDXP79C

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE**