



Transformer

by ABB





1M000000

Catalog Number 9T10C1535 **Type** QL

112.5 KVA 60 HZ 3 PH 5.6 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 240 VOLTS (LINE-LINE)
SECONDARY (H) 480 VOLTS (LINE-LINE)
277 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	
TAP	VOLTS
1-2	250
2-3	245
3-4	240
4-5	234
5-6	228
6-7	223
7-8	217



NET WGT
790 LB
358.3 Kg
89763
DY75C

INSPECTION & FINAL TEST
NOG
N137!
091021



LISTED 769G

H3 - H2 - H1 - -

- X3 - X2 - X1

H3 - H2 - H1 -

- X3 - X2 - X1

H0

2M000000

3M000000

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

H3 - H2 - H1 - -

- X3 - X2 - X1

Note: H0 at the bottom

Outline: 303B111GEDYP75C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency