



Transformer

by ABB



1M000000



Catalog Number

Type QL


9T33A2672

37.5 KVA 60 HZ 1 PH 5.4 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H2		SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
215	8-H1,7-H2	429	8-7
229	6-H1,5-H2	444	7-6
240	4-H1,3-H2	458	6-5
251	2-H1,1-H2	469	5-4
		480	4-3
		491	3-2
		502	2-1



COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

NET WGT 460 LB
208.7 Kg
90123
YX172

NOG O91021
INSPECTION & FINAL TEST N137!



X4	-	X4	-
X2	-	X2	-
X1	-	X1	-
H1	-	H1	-
H2	-	H2	-
X3	-	X3	-
H1	-	H1	-

Barcode: *2M0000000*

Barcode: *3M0000000*

ASSEMBLED IN MEXICO

X3 - X1 - X2 - X4
- H2 - H1 - - -

Note:

Outline: 303B409CAP072