



Transformer



Catalog Number **9Q1A015AJAS01A2T00** Type QL

9T83B2130G03

15.0 KVA 60 HZ 1 PH 3.2 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG

PRIMARY LINES ON X1-X2		SECONDARY LINES ON H1-H4	
VOLTS	CONNECT	VOLTS	CONNECT
207	14-X1,13-X2	120	H1-H3,H2-H4
213	12-X1,11-X2	240	H2-H3
219	10-X1,9-X2		
225	8-X1,7-X2		
230	6-X1,5-X2		
237	4-X1,3-X2		
240	2-X1,1-X2		

NET WGT
320 LB


145.2 Kg

50029

070115

INSPECTION
&
FINAL TEST

N5271



COIL TAP ARRANGEMENT



LISTED 769G

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

H3 - H4 - H2 - H1
- X2 - X1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

H1 - - -
H2 - - -
H3 - - -
H4 - - -
X1 - - -
X2 - - -

