



Transformer




Catalog Number **9Q1A025AXAS01C2T30** Type QL

9T83B2671G93

25.0 KVA 60 HZ 1 PH 6 % IMP

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

NOG




ELECTROSTATIC GROUND SHIELD IN EACH PHASE

PRIMARY		SECONDARY	
UOLTS	CONNECT	UOLTS	CONNECT
216	8-H1,7-H2	120	X1-X3,X2-X4
228	6-H1,5-H2	240	X2-X3
240	4-H1,3-H2		
252	2-H1,1-H2		
		432	8-7
		444	7-6
		456	6-5
		468	5-4
		480	4-3
		492	3-2

NET WGT
320 LB
145.2 Kg
50077
070115

INSPECTION & FINAL TEST
N5271

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1
- H2 - H1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X1 - - -
X2 - - -
- H1 - - -
X4 - X4 - X4 -
- H2 - H2 -
X3 - - -

