



Transformer




Catalog Number **9Q1A030AXAS00A2T00** Type **QL**

9T83B2672G51

30.0 KVA 60 HZ 1 PH 6.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY			
UOLTS	CONNECT	UOLTS	CONNECT
216	8-H1,7-H2	432	8-7
228	6-H1,5-H2	444	7-6
240	4-H1,3-H2	456	6-5
252	2-H1,1-H2	468	5-4
		480	4-3
		492	3-2

SECONDARY			
LINES ON X1-X4			
UOLTS	CONNECT	UOLTS	CONNECT
120	X1-X3,X2-X4		
240	X2-X3		

NET WGT
320 LB
145.2 Kg



50069

070115

INSPECTION
&
FINAL TEST

N5271

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R. ENCLOSURE (IP32) WHEN PROVIDED SHIELD. 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1

- H2 - H1 - -

Note: Standard

X1
-
X2
-
- H1
X4
- H2
X3



-
-
X2
- H1
X4
- H2
X3

