



Transformer



Catalog Number **9Q1A015AWAS00A2T00** Type **QL**

9T83B2680


15.0 KVA

60 HZ

1 PH 3.4 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY		SECONDARY	
UOLTS	CONNECT	UOLTS	CONNECT
270	8-H1,7-H2	540	8-7
285	6-H1,5-H2	555	7-6
300	4-H1,3-H2	570	6-5
315	2-H1,1-H2	585	5-4
		600	4-3
		615	3-2

SECONDARY	
UOLTS	CONNECT
120	X1-X3,X2-X4
240	X2-X3

NET WGT
320 LB
145.2 Kg



50064

070115

INSPECTION
&
FINAL TEST

N5271

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1

- H2 - H1 - -

Note: Standard

X1 -
X2 -
X3 -
X4 -
H1 -
H2 -



X1 -
X2 -
X3 -
X4 -
H1 -
H2 -

