



Transformer




Catalog Number **9T83B2710** Type **QL**

15.0 KVA 60 HZ 1 PH 3.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG




PRIMARY				SECONDARY	
UOLTS	CONNECT	UOLTS	CONNECT	UOLTS	CONNECT
108	8-X1,7-X2	216	8-7	240	H1-H3,H2-H4
114	6-X1,5-X2	222	7-6	480	H2-H3
120	4-X1,3-X2	228	6-5		
126	2-X1,1-X2	234	5-4		
		240	4-3		
		246	3-2		

NET WGT
320 LB
145.2 Kg

50095
070115

INSPECTION
&
FINAL TEST
N5271

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

H3 - H4 - H2 - H1
- X2 - X1 - -

Note: Standard

H1 -
H2 -
H3 -
H4 -
X1 -
X2 -



H1 -
H2 -
H3 -
H4 -
X1 -
X2 -

