



Transformer



Catalog Number **9Q1A025AZAS00A2T00** Type **QL**

9T83B2781

25.0 KVA 60 HZ 1 PH 5.6 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG

PRIMARY LINES ON X1-X2		SECONDARY LINES ON H1-H4	
VOLTS	CONNECT	VOLTS	CONNECT
198	14-X1,13-X2	120	H1-H3,H2-H4
204	12-X1,11-X2	240	H2-H3
210	10-X1,9-X2		
216	8-X1,7-X2		
220	6-X1,5-X2		
225	4-X1,3-X2		
231	2-X1,1-X2		

NET WGT

320 LB

145.2 Kg

50105


070115

INSPECTION



&

FINAL TEST

N5271



COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

H3 - H4 - H2 - H1


- X2 - X1 - -

Note: Standard

H1 - H2 - H3 - H4 - X1 - X2



2M000000



3M000000