



Transformer

Catalog Number

9T83B3389G03

500.0 KVA 60 HZ 3 PH 7.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C Type: QL

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 220 VOLTS (LINE-LINE)
 127 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G68


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER


Meets TP-1 2002 efficiency



JUMPER CONNECTION

TAP	VOLTS
1-2	508
2-3	490
3-4	480
4-5	472
5-6	454
6-7	445
7-8	435

COIL TAP ARRANGEMENT



NET WGT 3400 LB 1542.2 Kg

092915 N540! YF379
57899 NOG



LISTED 769G

Outline: 303B919AAP179
Assembled in Mexico

INSPECTION & FINAL TEST
N540!

