

Transformer

NEMA CLASS AA DRY TYPE TRANSFORMER



1M000000

X1 -
X2 -
X3 -
X4 -
H1 -
H2 -

X3 -
X4 -
X2 -
X1 -
H2 -
H1 -

Catalog Number Type QL


9Q1C025AXAS00A2T30

9T83C2571G50

25.0 KVA 60 HZ 1 PH 5.9 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG




PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
217	8-H1, 7-H2	433	8-7	120	X1-X3, X2-X4	240	X2-X3
228	6-H1, 5-H2	445	7-6				
240	4-H1, 3-H2	457	6-5				
252	2-H1, 1-H2	468	5-4				
		480	4-3				
		492	3-2				
		503	2-1				


NET WGT
350 LB
158.8 Kg
YF171
59116
012716

INSPECTION & FINAL TEST
N605!

COIL TAP



MENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1
- H2 - H1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard