



# Transformer

NEMA CLASS AA DRY TYPE TRANSFORMER



\*1M000000\*

Catalog Number


Type QL

9T83S2670

15.0 KVA 60 HZ 1 PH 4.2 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT		
216	8-H1,7-H2	431	8-7	120	X1-X3,X2-X4		
229	6-H1,5-H2	445	7-6	240	X2-X3		
240	4-H1,3-H2	458	6-5				
251	2-H1,1-H2	470	5-4				
		480	4-3				
		491	3-2				
		502	2-1				

NET WGT  
320 LB  
145.2 Kg  
YF171  
60317  
021216

INSPECTION & FINAL TEST  
N607!

### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18S4317G05

Outline: 303B406SAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X3 - X4 - X2 - X1  
- H2 - H1 - -

Note: Standard

X1 - X2 - X3 - X4 - H1 - H2

X1 - X2 - X3 - X4 - H1 - H2



\*2M000000\*



\*3M000000\*