



Transformer


Catalog Number 9T83W3878G15

300.0 KVA 60 HZ 3 PH 2.5 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C Type: Q1


Note: Design is based on 500.0KVA & 150C Rise 4.4% Imp.

PRIMARY (H)	480 VOLTS (LINE-LINE)
SECONDARY (X)	208 VOLTS (LINE-LINE)
	120 VOLTS (LINE-NEUTRAL)



JUMPER CONNECTION	
TAP	VOLTS
1-2	500
2-3	490
3-4	480
4-5	470
5-6	460
6-7	440
7-8	430

COIL TAP



NET WGT 2265 LB 1027.4 Kg

101415	N542!	L39AA
	57942	NOG



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18W4322G68

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



LISTED 769G

Outline: 303B912MVP179
Assembled in Mexico

INSPECTION & FINAL TEST
N542!