

**GE Energy**  
**300 Garlington Road**  
**Greenville, SC 29615**

**Panel type:** Dry Type XFRM Core & Coil

**Order no:**

**Serial no:** 1M00000000

**Date of manufacture:** 033016

**Rated voltage/ Phase:** Primary: 690Vac 3Phase

**Frequency:** Secondary: 400/381/208 Vac 60Hz

**Secondary Protection:** 250/ 50Amp Fuses

**Enclosure Rating:** IP42, NEMA 2 or No IP or  
NEMA Rating for non enclosure

**Max. Ambient Temperature:** 40 degrees C

**Field Cable Connections:** Use copper wire only

**Min. cable temp. rating:** 90 degrees C

**Made by:** GE Energy Industrial Solutions

Productos de Control S.A. de C.V.Avenida de los #136  
Nogales Sonora, Mexico 84090

**-10T1**  
**150kVA Transformer**  
**400/381/208 Vac**