

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0035	9T58R0035	1	50	CU	0.08	130/240	12/24	55	40	8100	NONE	Screw Terminals
9T58K0042	9T58R0042	1	60	CU	0.05	240x480	115	55	40	6100	NONE	Screw Terminals
9T58K0043	9T58R0043	1	60	CU	0.08	240x480	120	55	40	6125	NONE	Screw Terminals
9T58K0044	9T58R0044	1	60	CU	0.10	240x480	115	55	40	8100	NONE	Screw Terminals
9T58K0045	9T58R0045	1	60	CU	0.15	240x480	115	55	40	8150	NONE	Screw Terminals
9T58K0046	9T58R0046	1	60	CU	0.20	240x480	115	80	40	8175	NONE	Screw Terminals
9T58K0047	9T58R0047	1	60	CU	0.25	240x480	115	80	40	8200	NONE	Screw Terminals
9T58K0048	9T58R0048	1	60	CU	0.30	240x480	115	80	40	8250	NONE	Screw Terminals
9T58K0049	9T58R0049	1	60	CU	0.38	240x480	115	100	40	8250	NONE	Screw Terminals
9T58K0050	9T58R0050	1	60	CU	0.50	240x480	115	80	40	10225	NONE	Screw Terminals
9T58K0051	9T58R0051	1	60	CU	0.75	240x480	115	80	40	12225	NONE	Screw Terminals
9T58K0052	9T58R0052	1	60	CU	1.00	240x480	115	80	40	12300	NONE	Screw Terminals
9T58K0053	9T58R0053	1	60	CU	1.50	240x480	115	100	40	14225	NONE	Screw Terminals
9T58K0054	9T58R0054	1	60	CU	2.00	240x480	120	100	40	14300	NONE	Screw Terminals
9T58K0055	9T58R0055	1	60	CU	3.00	240x480	115	115	40	14475	NONE	Screw Terminals
9T58K0062	9T58R0062	1	50	CU	0.05	230/460/575	115/95	55	40	6150	NONE	Screw Terminals
9T58K0063	9T58R0063	1	50	CU	0.08	230/460/575	115/95	55	40	8100	NONE	Screw Terminals
9T58K0064	9T58R0064	1	50	CU	0.10	230/460/575	115/95	55	40	8150	NONE	Screw Terminals
9T58K0065	9T58R0065	1	50	CU	0.15	230/460/575	115/95	80	40	8200	NONE	Screw Terminals
9T58K0066	9T58R0066	1	50	CU	0.20	230/460/575	115/95	100	40	8200	NONE	Screw Terminals
9T58K0067	9T58R0067	1	50	CU	0.25	230/460/575	115/95	100	40	8250	NONE	Screw Terminals
9T58K0068	9T58R0068	1	50	CU	0.30	230/460/575	115/95	80	40	10225	NONE	Screw Terminals
9T58K0069	9T58R0069	1	50	CU	0.38	230/460/575	115/95	80	40	10225	NONE	Screw Terminals
9T58K0070	9T58R0070	1	50	CU	0.50	230/460/575	115/95	115	40	10225	NONE	Screw Terminals
9T58K0071	9T58R0071	1	50	CU	0.75	230/460/575	115/95	100	40	12300	NONE	Screw Terminals
9T58K0072	9T58R0072	1	50	CU	1.00	230/460/575	115/95	100	40	14225	NONE	Screw Terminals
9T58K0073	9T58R0073	1	50	CU	1.50	230/460/575	115/95	100	40	14300	NONE	Screw Terminals
9T58K0074	9T58R0074	1	50	CU	2.00	230/460/575	115/95	100	40	14475	NONE	Screw Terminals
9T58K0075	9T58R0075	1	60	CU	3.00	230x460	115	115	40	14475	NONE	Screw Terminals
9T58K0077	9T58R0077	1	60	CU	3.00	460/575	115	115	40	14475	NONE	Screw Terminals
9T58K0082	9T58R0082	1	50	CU	0.05	208/277/380	115/95	55	40	6150	NONE	Screw Terminals
9T58K0083	9T58R0083	1	50	CU	0.08	208/277/380	115/95	55	40	8100	NONE	Screw Terminals
9T58K0084	9T58R0084	1	50	CU	0.10	208/277/380	115/95	55	40	8150	NONE	Screw Terminals
9T58K0085	9T58R0085	1	50	CU	0.15	208/277/380	115/95	80	40	8200	NONE	Screw Terminals
9T58K0086	9T58R0086	1	50	CU	0.20	208/277/380	115/95	100	40	8200	NONE	Screw Terminals
9T58K0087	9T58R0087	1	50	CU	0.25	208/277/380	115/95	100	40	8250	NONE	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0088	9T58R0088	1	50	CU	0.30	208/277/380	115/95	80	40	10225	NONE	Screw Terminals
9T58K0089	9T58R0089	1	50	CU	0.38	208/277/380	115/95	80	40	10225	NONE	Screw Terminals
9T58K0090	9T58R0090	1	50	CU	0.50	208/277/380	115/95	115	40	10225	NONE	Screw Terminals
9T58K0091	9T58R0091	1	50	CU	0.75	208/277/380	115/95	80	40	12300	NONE	Screw Terminals
9T58K0092	9T58R0092	1	50	CU	1.00	208/277/380	115/95	100	40	14225	NONE	Screw Terminals
9T58K0093	9T58R0093	1	50	CU	1.50	208/277/380	115/95	100	40	14300	NONE	Screw Terminals
9T58K0094	9T58R0094	1	50	CU	2.00	208/277/380	115/95	100	40	14475	NONE	Screw Terminals
9T58K0095	9T58R0095	1	60	CU	3.00	208/277	115	115	40	14475	NONE	Screw Terminals
9T58K0727	9T58R0727	1	50	CU	0.10	400	120	55	40	8150	NONE	Screw Terminals
9T58K0728	9T58R0728	1	50	CU	0.25	380/415/480	120	100	40	8250	NONE	Screw Terminals
9T58K0945	9T58R0945	1	50	CU	0.50	380/415/480	120	100	40	12225	NONE	Screw Terminals
9T58K0946	9T58R0946	1	50	CU	0.50	230	208	115	40	10225	NONE	Screw Terminals
9T58K0947	9T58R0947	1	50	CU	0.50	600	208	115	40	10225	NONE	Screw Terminals
9T58K0948	9T58R0948	1	50	CU	1.00	230	208	115	40	12300	NONE	Screw Terminals
9T58K0949	9T58R0949	1	50	CU	1.00	480	208	115	40	12300	NONE	Screw Terminals
9T58K0950	9T58R0950	1	50	CU	1.00	600	208	115	40	12300	NONE	Screw Terminals
9T58K1000	9T58R1000	1	60	CU	0.75	120x240	75	100	40	12225	NONE	Screw Terminals
9T58K1012	9T58R1012	1	60	CU	1.00	480	220	100	40	12300	NONE	Screw Terminals
9T58K1015	9T58R1015	1	60	CU	3.00	480	220	100	40	14475	NONE	Screw Terminals
9T58K1101	9T58R1101	1	50	CU	0.10	415	110	55	40	8150	NONE	Screw Terminals
9T58K1692	9T58R1692	1	50	CU	1.65	330	158	115	40	12300	NONE	Screw Terminals
9T58K1695	9T58R1695	1	60	CU	0.15	277	12/24	55	40	8150	NONE	Screw Terminals
9T58K1696	9T58R1696	1	50	CU	1.20	240	105	115	40	12300	NONE	Screw Terminals
9T58K1697	9T58R1697	1	50	CU	0.87	330	158	115	40	10225	NONE	Screw Terminals
9T58K1698	9T58R1698	1	60	CU	1.50	120	90	100	40	14225	NONE	Screw Terminals
9T58K2802	9T58R2802	1	60	CU	0.05	240x480	120/240	55	40	6100	NONE	Screw Terminals
9T58K2803	9T58R2803	1	60	CU	0.08	240x480	120/240	55	40	6125	NONE	Screw Terminals
9T58K2804	9T58R2804	1	60	CU	0.10	240x480	120/240	55	40	8100	NONE	Screw Terminals
9T58K2805	9T58R2805	1	60	CU	0.15	240x480	120/240	55	40	8150	NONE	Screw Terminals
9T58K2806	9T58R2806	1	60	CU	0.20	240x480	120/240	80	40	8175	NONE	Screw Terminals
9T58K2807	9T58R2807	1	60	CU	0.25	240x480	120/240	80	40	8200	NONE	Screw Terminals
9T58K2808	9T58R2808	1	60	CU	0.30	240x480	120/240	100	40	8200	NONE	Screw Terminals
9T58K2809	9T58R2809	1	60	CU	0.38	240x480	120/240	100	40	8250	NONE	Screw Terminals
9T58K2810	9T58R2810	1	60	CU	0.50	240x480	120/240	100	40	10225	NONE	Screw Terminals
9T58K2811	9T58R2811	1	60	CU	0.75	240x480	120/240	100	40	12225	NONE	Screw Terminals
9T58K2812	9T58R2812	1	60	CU	1.00	240x480	120/240	100	40	12300	NONE	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2813	9T58R2813	1	60	CU	1.50	240x480	120/240	100	40	14225	NONE	Screw Terminals
9T58K2814	9T58R2814	1	60	CU	2.00	240x480	120/240	100	40	14300	NONE	Screw Terminals
9T58K2815	9T58R2815	1	60	CU	3.00	240x480	120/240	100	40	14475	NONE	Screw Terminals
9T58K2823	9T58R2823	1	60	CU	0.08	600	120/240	55	40	6125	NONE	Screw Terminals
9T58K2824	9T58R2824	1	60	CU	0.10	600	120/240	55	40	8100	NONE	Screw Terminals
9T58K2826	9T58R2826	1	60	CU	0.20	600	120/240	80	40	8175	NONE	Screw Terminals
9T58K2827	9T58R2827	1	60	CU	0.25	600	120/240	80	40	8200	NONE	Screw Terminals
9T58K2828	9T58R2828	1	60	CU	0.30	600	120/240	100	40	8200	NONE	Screw Terminals
9T58K2830	9T58R2830	1	60	CU	0.50	600	120/240	80	40	10225	NONE	Screw Terminals
9T58K2831	9T58R2831	1	60	CU	0.75	600	120/240	100	40	12225	NONE	Screw Terminals
9T58K2832	9T58R2832	1	60	CU	1.00	600	120/240	115	40	12300	NONE	Screw Terminals
9T58K2833	9T58R2833	1	60	CU	1.50	600	120/240	100	40	14225	NONE	Screw Terminals
9T58K2834	9T58R2834	1	60	CU	2.00	600	120/240	100	40	14300	NONE	Screw Terminals
9T58K2835	9T58R2835	1	60	CU	3.00	600	120/240	100	40	14475	NONE	Screw Terminals
9T58K2873	9T58R2873	1	60	CU	0.05	120x240	12/24	55	40	6100	NONE	Screw Terminals
9T58K2874	9T58R2874	1	60	CU	0.08	120x240	12/24	55	40	6125	NONE	Screw Terminals
9T58K2875	9T58R2875	1	60	CU	0.10	120x240	12/24	55	40	8100	NONE	Screw Terminals
9T58K2876	9T58R2876	1	60	CU	0.15	120x240	12/24	55	40	8150	NONE	Screw Terminals
9T58K2877	9T58R2877	1	60	CU	0.20	120x240	12/24	80	40	8175	NONE	Screw Terminals
9T58K2878	9T58R2878	1	60	CU	0.25	120x240	12/24	100	40	8200	NONE	Screw Terminals
9T58K2879	9T58R2879	1	60	CU	0.30	120x240	12/24	100	40	8200	NONE	Screw Terminals
9T58K2890	9T58R2890	1	60	CU	0.08	120x240	16/32	55	40	8175	NONE	Screw Terminals
9T58K2892	9T58R2892	1	50	CU	0.10	115/120	13.4	115	40	8200	NONE	Screw Terminals
9T58K2893	9T58R2893	1	60	CU	0.20	120x240	16/32	80	40	8175	NONE	Screw Terminals
9T58K2907	9T58R2907	1	60	CU	0.10	120x240	120/240	55	40	8100	NONE	Screw Terminals
9T58K2909	9T58R2909	1	60	CU	0.20	120x240	120/240	80	40	8175	NONE	Screw Terminals
9T58K2911	9T58R2911	1	60	CU	0.30	120x240	120/240	100	40	8200	NONE	Screw Terminals
9T58K2913	9T58R2913	1	60	CU	0.50	120x240	120/240	80	40	10225	NONE	Screw Terminals
9T58K2914	9T58R2914	1	60	CU	0.75	120x240	120/240	100	40	12225	NONE	Screw Terminals
9T58K2915	9T58R2915	1	60	CU	1.00	120x240	120/240	115	40	12300	NONE	Screw Terminals
9T58K2917	9T58R2917	1	60	CU	2.00	120x240	120/240	100	40	14300	NONE	Screw Terminals
9T58K2918	9T58R2918	1	60	CU	3.00	120x240	120/240	115	40	14475	NONE	Screw Terminals
9T58K2930	9T58R2930	1	50	CU	0.50	240x480	120/240	115	40	10225	NONE	Screw Terminals
9T58K2931	9T58R2931	1	50	CU	0.75	240x480	120/240	100	40	12300	NONE	Screw Terminals
9T58K2932	9T58R2932	1	50	CU	1.00	240x480	120/240	100	40	14225	NONE	Screw Terminals
9T58K2933	9T58R2933	1	50	CU	1.50	240x480	120/240	100	40	14300	NONE	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2934	9T58R2934	1	50	CU	2.00	240x480	120/240	100	40	14475	NONE	Screw Terminals
9T58K2935	9T58R2935	1	50	CU	3.00	240x480	120/240	115	40	14475	NONE	Screw Terminals
9T58K2959	9T58R2959	1	50	CU	0.25	600	120/240	100	40	8200	NONE	Screw Terminals
9T58K2975	9T58R2975	1	50	CU	0.25	380/400/416	115/230	115	40	8200	NONE	Screw Terminals
9T58K2978	9T58R2978	1	50	CU	0.50	380/400/416	115/230	115	40	10225	NONE	Screw Terminals
9T58K2979	9T58R2979	1	50	CU	0.75	380/400/416	115/230	100	40	12300	NONE	Screw Terminals
9T58K2980	9T58R2980	1	50	CU	1.00	380/400/416	115/230	100	40	14225	NONE	Screw Terminals
9T58K2981	9T58R2981	1	50	CU	1.50	380/400/416	115/230	100	40	14300	NONE	Screw Terminals
9T58K2982	9T58R2982	1	50	CU	2.00	380/400/416	115/230	100	40	14475	NONE	Screw Terminals
9T58K2983	9T58R2983	1	50	CU	3.00	380/400/416	115/230	115	40	14475	NONE	Screw Terminals
9T58K2984	9T58R2984	1	50	CU	2.00	200/208/240/380/416	115/230	100	40	14475	NONE	Screw Terminals
9T58K2985	9T58R2985	1	50	CU	1.00	380/416/460	115/230	100	40	14225	NONE	Screw Terminals
9T58K3005	9T58R3005	1	60	CU	0.35	208/230	115	100	40	8250	NONE	Screw Terminals
9T58K3010	9T58R3010	1	50	CU	0.25	208/230/460	115/95	100	40	8250	NONE	Screw Terminals
9T58K3015	9T58R3015	1	60	CU	0.28	240x480	80/115/230	100	40	10225	NONE	Screw Terminals
9T58K3023	9T58R3023	1	50	CU	1.50	380/400/415	82	100	40	14300	NONE	Screw Terminals
9T58K3024	9T58R3024	1	60	CU	0.25	240x480	12/24	80	40	8200	NONE	Screw Terminals
9T58K3027	9T58R3027	1	60	CU	0.10	240x480	24	55	40	8100	NONE	Screw Terminals
9T58K3028	9T58R3028	1	60	CU	0.15	240x480	24	55	40	8150	NONE	Screw Terminals
9T58K3092	9T58R3092	1	50	CU	0.25	208/240/480	115	100	40	8250	NONE	Screw Terminals
9T58K3101	9T58R3101	1	60	CU	0.08	208/230/460	115	55	40	6150	NONE	Screw Terminals
9T58K3113	9T58R3113	1	50	CU	0.50	380/480/575	120/240	115	40	10225	NONE	Screw Terminals
9T58K3120	9T58R3120	1	60	CU	0.10	208	12/24	55	40	8100	NONE	Screw Terminals
9T58K3127	9T58R3127	1	50	CU	0.15	400	105	55	40	8175	NONE	Screw Terminals
9T58K3128	9T58R3128	1	50	CU	0.50	400	105	55	40	12225	NONE	Screw Terminals
9T58K3135	9T58R3135	1	60	CU	0.25	240x480	115	55	40	8250	NONE	Screw Terminals
9T58K3144	9T58R3144	1	60	CU	1.00	208	120/240	100	40	12300	NONE	Screw Terminals
9T58K3145	9T58R3145	1	50	CU	1.00	200/220	120/240	100	40	14225	NONE	Screw Terminals
9T58K3154	9T58R3154	1	50	CU	0.05	380/460/575	24	55	40	6150	NONE	Screw Terminals
9T58K3158	9T58R3158	1	60	CU	0.50	208/240/480	12/24	100	40	10225	NONE	Screw Terminals
9T58K3159	9T58R3159	1	60	CU	0.15	208/240	27	100	40	8175	NONE	Screw Terminals
9T58K3160	9T58R3160	1	60	CU	0.25	230x460	120/240	100	40	8200	NONE	Screw Terminals
9T58K3161	9T58R3161	1	60	CU	0.05	208/230/460	120	55	40	6100	NONE	Screw Terminals
9T58K3164	9T58R3164	1	60	CU	0.05	240x480	12/24	55	40	6100	NONE	Screw Terminals
9T58K3167	9T58R3167	1	60	CU	0.30	480	24	100	40	8200	NONE	Screw Terminals
9T58K3172	9T58R3172	1	60	CU	2.00	240x480	115	55	40	14475	NONE	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K3204	9T58R3204	1	50	CU	0.75	208/230/460	115/95	100	40	12300	NONE	Screw Terminals
9T58K3205	9T58R3205	1	50	CU	1.00	208/230/460	115/95	100	40	14225	NONE	Screw Terminals
9T58K3206	9T58R3206	1	50	CU	2.00	208/230/460	115/95	100	40	14475	NONE	Screw Terminals
9T58K3215	9T58R3215	1	50	CU	0.50	208/230/460	115/95	115	40	10225	NONE	Screw Terminals
9T58K3216	9T58R3216	1	50	CU	1.50	208/230/460	115/95	100	40	14300	NONE	Screw Terminals
9T58K3263	9T58R3263	1	60	CU	0.50	208/240/480	120	115	40	10225	NONE	Screw Terminals
9T58K3301	9T58R3301	1	60	CU	0.50	240x480	115	55	40	12300	NONE	Screw Terminals
9T58K3302	9T58R3302	1	60	CU	0.75	240x480	115	55	40	14225	NONE	Screw Terminals
9T58K3303	9T58R3303	1	60	CU	1.00	240x480	120	55	40	14300	NONE	Screw Terminals
9T58K3304	9T58R3304	1	60	CU	1.50	240x480	120	55	40	14300	NONE	Screw Terminals
9T58K3306	9T58R3306	1	50	CU	3.00	208x416	115	115	40	14475	NONE	Screw Terminals
9T58K3314	9T58R3314	1	60	CU	0.53	460	120-29	115	40	10225	NONE	Screw Terminals
9T58K3331	9T58R3331	1	60	CU	0.30	240x480	115	55	40	10225	NONE	Screw Terminals
9T58K3332	9T58R3332	1	60	CU	0.38	240x480	115	55	40	10225	NONE	Screw Terminals
9T58K3366	9T58R3366	1	60	CU	2.00	240x480	480/240	115	40	14475	NONE	Screw Terminals
9T58K3396	9T58R3396	1	50	CU	1.50	215/240/260	115	100	40	14300	NONE	Screw Terminals
9T58K3413	9T58R3413	1	50	CU	0.38	220/575	24	100	40	12225	NONE	Screw Terminals
9T58K3458	9T58R3458	1	50	CU	0.25	120/126	200/210/220	100	40	8250	NONE	Screw Terminals
9T58K3466	9T58R3466	1	60	CU	0.05	208/230/460	115/120	55	40	6125	NONE	Screw Terminals
9T58K3479	9T58R3479	1	50	CU	0.15	195	12/24	80	40	8175	NONE	Screw Terminals
9T58K3552	9T58R3552	1	50	CU	0.38	200/220/440	24	100	40	10225	NONE	Screw Terminals
9T58K3559	9T58R3559	1	50	CU	2.00	240x480	110/220	100	40	14475	NONE	Screw Terminals
9T58K3560	9T58R3560	1	60	CU	0.15	208/240/480	24-120	100	40	8200	NONE	Screw Terminals
9T58K3564	9T58R3564	1	60	CU	1.00	277	120	100	40	12300	NONE	Screw Terminals
9T58K3715	9T58R3715	1	50	CU	0.25	230/400/460/575	115/95/125	80	40	10225	NONE	Screw Terminals
9T58K3716	9T58R3716	1	50	CU	0.35	230/400/460/575	115/95/125	100	40	10225	NONE	Screw Terminals
9T58K3717	9T58R3717	1	50	CU	0.50	230/400/460/575	115/95/125	115	40	12225	NONE	Screw Terminals
9T58K3718	9T58R3718	1	50	CU	0.75	230/400/460/575	115/95/125	100	40	12300	NONE	Screw Terminals
9T58K3719	9T58R3719	1	50	CU	1.00	230/400/460/575	115/95/125	100	40	14225	NONE	Screw Terminals
9T58K3720	9T58R3720	1	50	CU	1.50	230/400/460/575	115/95/125	115	40	14300	NONE	Screw Terminals
9T58K3721	9T58R3721	1	50	CU	2.00	230/400/460/575	115/95/125	115	40	14475	NONE	Screw Terminals
9T58K3730	9T58R3730	1	50	CU	1.00	230/460/575	115	115	40	14225	NONE	Screw Terminals
9T58K3923	9T58R3923	1	60	CU	0.50	220	120	115	40	8200	NONE	Screw Terminals
9T58K3924	9T58R3924	1	60	CU	0.75	220	120	115	40	8250	NONE	Screw Terminals
9T58K3926	9T58R3926	1	50	CU	0.75	100	230	115	40	10225	NONE	Screw Terminals
9T58K3927	9T58R3927	1	50	CU	1.00	100	230	115	40	10225	NONE	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K3931	9T58R3931	1	60	CU	0.90	332	266	115	40	8175	NONE	Screw Terminals
9T58K4033	9T58R4033	1	50	CU	0.50	380/460	120-24	115	40	10225	NONE	Screw Terminals
9T58K4050	9T58R4050	1	60	CU	0.05	208/240	12/24	55	40	6100	NONE	Screw Terminals
9T58K4051	9T58R4051	1	60	CU	0.10	208/240	12/24	55	40	8100	NONE	Screw Terminals
9T58K4052	9T58R4052	1	60	CU	0.15	208/240	12/24	55	40	8150	NONE	Screw Terminals
9T58K4053	9T58R4053	1	60	CU	0.25	208/240	12/24	100	40	8200	NONE	Screw Terminals
9T58K4132	9T58R4132	1	60	CU	0.10	240x480	12/24	55	40	8100	NONE	Screw Terminals
9T58K4133	9T58R4133	1	60	CU	0.15	240x480	12/24	55	40	8150	NONE	Screw Terminals
9T58K4136	9T58R4136	1	60	CU	0.05	220/380/460	120	55	40	6125	NONE	Screw Terminals
9T58K4137	9T58R4137	1	60	CU	0.08	220/380/460	24	55	40	8100	NONE	Screw Terminals
9T58K4141	9T58R4141	1	60	CU	1.00	150/208/220/240	70	100	40	14225	NONE	Screw Terminals
9T58K4152	9T58R4152	1	60	CU	0.20	208/240/480	120	80	40	8200	NONE	Screw Terminals
9T58K4159	9T58R4159	1	60	CU	0.50	208/230/460	115	115	40	10225	NONE	Screw Terminals
9T58K4161	9T58R4161	1	50	CU	0.50	208/230/460	115	115	40	12225	NONE	Screw Terminals
9T58K4166	9T58R4166	1	50	CU	0.05	120x240	12/24	55	40	6100	NONE	Screw Terminals
9T58K4176	9T58R4176	1	60	CU	0.50	480	277	100	40	10225	NONE	Screw Terminals
9T58K4178	9T58R4178	1	50	CU	0.25	380/415/575	24	100	40	10225	NONE	Screw Terminals
9T58K4179	9T58R4179	1	60	CU	0.25	208/240/480	24	100	40	8250	NONE	Screw Terminals
9T58K4180	9T58R4180	1	60	CU	2.00	380/460	115	100	40	14300	NONE	Screw Terminals
9T58K4183	9T58R4183	1	60	CU	0.20	208/240/480	24	100	40	8200	NONE	Screw Terminals
9T58K4184	9T58R4184	1	50	CU	0.15	230x460	120-24	100	40	10225	NONE	Screw Terminals
9T58K4186	9T58R4186	1	60	CU	0.30	208/230/380/460/575	115	100	40	10225	NONE	Screw Terminals
9T58K4190	9T58R4190	1	60	CU	0.05	208/240/480	24-120	55	40	6150	NONE	Screw Terminals
9T58K4191	9T58R4191	1	60	CU	0.10	208/240/480	24-120	55	40	8150	NONE	Screw Terminals
9T58K4193	9T58R4193	1	50	CU	0.25	208/230/460	24-115	115	40	12225	NONE	Screw Terminals
9T58K4194	9T58R4194	1	60	CU	0.25	208/240/480	24-120	100	40	10225	NONE	Screw Terminals
9T58K4205	9T58R4205	1	50	CU	1.57	210/230/240	24-110/120	115	40	14300	NONE	Screw Terminals
9T58K4206	9T58R4206	1	50	CU	0.57	210/230/240	24-110/120	115	40	12225	NONE	Screw Terminals
9T58K4207	9T58R4207	1	60	CU	0.58	200/230/460/575	24-120	100	40	12225	NONE	Screw Terminals
9T58K4208	9T58R4208	1	50	CU	0.58	380/415	24-120	100	40	12225	NONE	Screw Terminals
9T58K4210	9T58R4210	1	50	CU	0.86	120/240/480	22-80	100	40	14225	NONE	Screw Terminals
9T58K4277	9T58R4277	1	50	CU	0.75	200/220/230/380/400/415	117	115	40	12300	NONE	Screw Terminals
9T58K4290	9T58R4290	1	60	CU	0.50	208	120/240	100	40	10225	NONE	Screw Terminals
9T58K4299	9T58R4299	1	50	CU	0.20	240x480	120	115	40	8175	NONE	Screw Terminals
9T58K4350	9T58R4350	1	50	CU	0.08	120/240	12/24	55	40	8100	NONE	Screw Terminals
9T58K4355	9T58R4355	1	60	CU	0.50	220x440	110/220	100	40	12225	NONE	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K4356	9T58R4356	1	60	CU	0.75	220x440	110/220	100	40	12300	NONE	Screw Terminals
9T58K4357	9T58R4357	1	60	CU	1.00	220x440	110/220	100	40	14225	NONE	Screw Terminals
9T58K4358	9T58R4358	1	60	CU	1.50	220x440	110/220	80	40	14300	NONE	Screw Terminals
9T58K4359	9T58R4359	1	60	CU	2.00	220x440	110/220	100	40	14475	NONE	Screw Terminals
9T58K4360	9T58R4360	1	50	CU	0.10	380/415	24	55	40	8150	NONE	Screw Terminals
9T58K4365	9T58R4365	1	60	CU	0.50	220x440	110/220	100	40	12225	NONE	Screw Terminals
9T58K4366	9T58R4366	1	60	CU	0.75	220x440	110/220	100	40	12300	NONE	Screw Terminals
9T58K4367	9T58R4367	1	60	CU	1.00	220x440	110/220	100	40	14225	NONE	Screw Terminals
9T58K4368	9T58R4368	1	60	CU	1.50	220x440	110/220	80	40	14300	NONE	Screw Terminals
9T58K4369	9T58R4369	1	60	CU	2.00	220x440	110/220	115	40	14475	NONE	Screw Terminals
9T58K4405	9T58R4405	1	60	CU	0.69	200/230/240/460/480	38.5	115	40	12225	NONE	Screw Terminals
9T58K4500	9T58R4500	1	60	CU	0.05	208	120	55	40	6100	NONE	Screw Terminals
9T58K4501	9T58R4501	1	60	CU	0.05	600	120	55	40	6100	NONE	Screw Terminals
9T58K4502	9T58R4502	1	60	CU	0.05	277	120	55	40	6100	NONE	Screw Terminals
9T58K4503	9T58R4503	1	60	CU	0.05	240x480	24	55	40	6100	NONE	Screw Terminals
9T58K4504	9T58R4504	1	60	CU	0.05	120	24	55	40	6100	NONE	Screw Terminals
9T58K4505	9T58R4505	1	60	CU	0.05	208	24	55	40	6100	NONE	Screw Terminals
9T58K4506	9T58R4506	1	60	CU	0.10	208	120	55	40	8150	NONE	Screw Terminals
9T58K4510	9T58R4510	1	60	CU	0.25	600	120	80	40	8200	NONE	Screw Terminals
9T58K4511	9T58R4511	1	60	CU	0.25	208	120	80	40	8200	NONE	Screw Terminals
9T58K4512	9T58R4512	1	60	CU	0.30	600	120	100	40	8250	NONE	Screw Terminals
9T58K4513	9T58R4513	1	60	CU	0.30	208	120	100	40	8250	NONE	Screw Terminals
9T58K4515	9T58R4515	1	60	CU	0.25	208/240/480	120	100	40	8250	NONE	Screw Terminals
9T58K4516	9T58R4516	1	60	CU	0.50	480	24	100	40	10225	NONE	Screw Terminals
9T58K5083	9T58R5083	1	50	CU	0.20	115x230	230/460	80	40	8200	NONE	Screw Terminals
9T58K6143	9T58R6143	1	50	CU	1.50	230/460/575	115	115	40	14300	NONE	Screw Terminals
9T58K7772	9T58R7772	1	60	CU	0.44	208/230/240/460/480	115	80	40	10225	NONE	Screw Terminals
9T58K7773	9T58R7773	1	60	CU	0.35	208/230/240/460/480	24/12-48/24	100	40	10225	NONE	Screw Terminals
9T58K7778	9T58R7778	1	60	CU	1.19	200/230/240/460/480	38.5-115	80	40	12300	NONE	Screw Terminals
9T58K7779	9T58R7779	1	50	CU	0.50	120x240	120/240	80	40	12225	NONE	Screw Terminals
9T58K7780	9T58R7780	1	60	CU	0.05	277	24	55	40	6100	NONE	Screw Terminals
9T58K7782	9T58R7782	1	50	CU	0.20	440/550	200	100	40	8200	NONE	Screw Terminals
9T58K9998	9T58R9998	1	60	CU	0.13	525	128/147	100	40	8175	NONE	Screw Terminals
9T58K0094	9T58R0094G07	1	50	CU	2.00	208/277/380	115/95	100	40	14475	NONE	Leads Out
9T58K0501	9T58R0501G07	1	60	CU	0.06	480	120	55	40	6100	NONE	Leads Out
9T58K0503	9T58R0503G07	1	60	CU	0.10	480	120	55	40	8100	NONE	Leads Out

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0504	9T58R0504G07	1	60	CU	0.15	480	120	55	40	8150	NONE	Leads Out
9T58K0507	9T58R0507G07	1	60	CU	0.30	480	120	80	40	8250	NONE	Leads Out
9T58K0511	9T58R0511G07	1	60	CU	0.06	208	120	55	40	6100	NONE	Leads Out
9T58K0513	9T58R0513G07	1	60	CU	0.10	208	120	55	40	8100	NONE	Leads Out
9T58K0517	9T58R0517G07	1	60	CU	0.30	208	120	115	40	8250	NONE	Leads Out
9T58K0531	9T58R0531G07	1	60	CU	0.06	600	120	55	40	6100	NONE	Leads Out
9T58K0533	9T58R0533G07	1	60	CU	0.10	600	120	55	40	8100	NONE	Leads Out
9T58K0534	9T58R0534G07	1	60	CU	0.15	600	120	55	40	8150	NONE	Leads Out
9T58K0537	9T58R0537G07	1	60	CU	0.30	600	120	80	40	8250	NONE	Leads Out
9T58K0574	9T58R0574G07	1	60	CU	0.15	240x480	120/240	55	40	8150	NONE	Leads Out
9T58K0577	9T58R0577G07	1	60	CU	0.30	240x480	120/240	80	40	8250	NONE	Leads Out
9T58K0702	9T58R0702G07	1	60	CU	0.15	480	24	55	40	8150	NONE	Leads Out
9T58K0705	9T58R0705G07	1	60	CU	0.30	480	24	80	40	8250	NONE	Leads Out
9T58K0944	9T58R0944G07	1	60	CU	0.15	208	120	55	40	8150	NONE	Leads Out
9T58K0953	9T58R0953G07	1	50	CU	0.10	380/400/416	110/220	55	40	8150	NONE	Leads Out
9T58K0954	9T58R0954G07	1	50	CU	0.15	380/400/415	110/220	80	40	8175	NONE	Leads Out
9T58K0956	9T58R0956G07	1	50	CU	0.25	380/400/416	110/220	80	40	8250	NONE	Leads Out
9T58K1669	9T58R1669G07	1	60	CU	2.00	575	460	115	40	14300	NONE	Leads Out
9T58K1802	9T58R1802G07	1	60	CU	0.05	240x480	120/240	55	40	6100	NONE	Leads Out
9T58K1803	9T58R1803G07	1	60	CU	0.08	240x480	120/240	55	40	6125	NONE	Leads Out
9T58K1804	9T58R1804G07	1	60	CU	0.10	240x480	120/240	55	40	8100	NONE	Leads Out
9T58K1805	9T58R1805G07	1	60	CU	0.15	240x480	120/240	55	40	8150	NONE	Leads Out
9T58K1806	9T58R1806G07	1	60	CU	0.20	240x480	120/240	80	40	8175	NONE	Leads Out
9T58K1807	9T58R1807G07	1	60	CU	0.25	240x480	120/240	80	40	8200	NONE	Leads Out
9T58K1808	9T58R1808G07	1	60	CU	0.30	240x480	120/240	100	40	8200	NONE	Leads Out
9T58K1809	9T58R1809G07	1	60	CU	0.38	240x480	120/240	100	40	8250	NONE	Leads Out
9T58K1810	9T58R1810G07	1	60	CU	0.50	240x480	120/240	100	40	10225	NONE	Leads Out
9T58K1811	9T58R1811G07	1	60	CU	0.75	240x480	120/240	100	40	12225	NONE	Leads Out
9T58K1812	9T58R1812G07	1	60	CU	1.00	240x480	120/240	100	40	12300	NONE	Leads Out
9T58K1813	9T58R1813G07	1	60	CU	1.50	240x480	120/240	100	40	14225	NONE	Leads Out
9T58K1814	9T58R1814G07	1	60	CU	2.00	240x480	120/240	100	40	14300	NONE	Leads Out
9T58K1815	9T58R1815G07	1	60	CU	3.00	240x480	120/240	100	40	14475	NONE	Leads Out
9T58K1824	9T58R1824G07	1	60	CU	0.10	600	120/240	55	40	8100	NONE	Leads Out
9T58K1826	9T58R1826G07	1	60	CU	0.20	600	120/240	80	40	8175	NONE	Leads Out
9T58K1828	9T58R1828G07	1	60	CU	0.30	600	120/240	100	40	8200	NONE	Leads Out
9T58K1830	9T58R1830G07	1	60	CU	0.50	600	120/240	100	40	10225	NONE	Leads Out



Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K1832	9T58R1832G07	1	60	CU	1.00	600	120/240	100	40	14225	NONE	Leads Out
9T58K1834	9T58R1834G07	1	60	CU	2.00	600	120/240	100	40	14300	NONE	Leads Out
9T58K1835	9T58R1835G07	1	60	CU	3.00	600	120/240	115	40	14475	NONE	Leads Out
9T58K1873	9T58R1873G07	1	60	CU	0.05	120x240	12/24	55	40	6100	NONE	Leads Out
9T58K1874	9T58R1874G07	1	60	CU	0.08	120x240	12/24	55	40	6125	NONE	Leads Out
9T58K1875	9T58R1875G07	1	60	CU	0.10	120x240	12/24	55	40	8100	NONE	Leads Out
9T58K1876	9T58R1876G07	1	60	CU	0.15	120x240	12/24	55	40	8150	NONE	Leads Out
9T58K1877	9T58R1877G07	1	60	CU	0.20	120x240	12/24	80	40	8175	NONE	Leads Out
9T58K1878	9T58R1878G07	1	60	CU	0.25	120x240	12/24	100	40	8200	NONE	Leads Out
9T58K1879	9T58R1879G07	1	60	CU	0.30	120x240	12/24	100	40	8200	NONE	Leads Out
9T58K1881	9T58R1881G07	1	60	CU	0.50	120x240	12/24	100	40	10225	NONE	Leads Out
9T58K1882	9T58R1882G07	1	60	CU	0.75	120x240	12/24	115	40	12225	NONE	Leads Out
9T58K1883	9T58R1883G07	1	50	CU	1.00	120x240	12/24	115	40	14225	NONE	Leads Out
9T58K1917	9T58R1917G07	1	60	CU	2.00	120x240	120/240	100	40	14300	NONE	Leads Out
9T58K1918	9T58R1918G07	1	60	CU	3.00	120x240	120/240	115	40	14475	NONE	Leads Out
9T58K1927	9T58R1927G07	1	50	CU	0.25	240x480	120/240	100	40	8200	NONE	Leads Out
9T58K1928	9T58R1928G07	1	50	CU	0.30	240x480	120/240	100	40	8250	NONE	Leads Out
9T58K1930	9T58R1930G07	1	50	CU	0.50	240x480	120/240	115	40	10225	NONE	Leads Out
9T58K1931	9T58R1931G07	1	50	CU	0.75	240x480	120/240	100	40	12300	NONE	Leads Out
9T58K1933	9T58R1933G07	1	50	CU	1.50	240x480	120/240	100	40	14300	NONE	Leads Out
9T58K1935	9T58R1935G07	1	50	CU	3.00	240x480	120/240	115	40	14475	NONE	Leads Out
9T58K1944	9T58R1944G07	1	50	CU	0.30	575	120	100	40	8250	NONE	Leads Out
9T58K1976	9T58R1976G07	1	50	CU	0.30	380/400/416	115/230	115	40	8250	NONE	Leads Out
9T58K1978	9T58R1978G07	1	50	CU	0.50	380/400/416	115/230	115	40	10225	NONE	Leads Out
9T58K1979	9T58R1979G07	1	50	CU	0.75	380/400/416	115/230	100	40	12300	NONE	Leads Out
9T58K1980	9T58R1980G07	1	50	CU	1.00	380/400/416	115/230	100	40	14225	NONE	Leads Out
9T58K1981	9T58R1981G07	1	50	CU	1.50	380/400/416	115/230	100	40	14300	NONE	Leads Out
9T58K2894	9T58R2894G07	1	50	CU	1.00	120x240	16/32	115	40	14225	NONE	Leads Out
9T58K3020	9T58R3020G07	1	60	CU	0.05	208/240/277/380/480	24	55	40	6125	NONE	Leads Out
9T58K3165	9T58R3165G07	1	50	CU	0.10	208/240/380/480	24	55	40	8150	NONE	Leads Out
9T58K3166	9T58R3166G07	1	60	CU	0.15	480	277	55	40	8150	NONE	Leads Out
9T58K3218	9T58R3218G07	1	60	CU	0.50	550	240	100	40	10225	NONE	Leads Out
9T58K3227	9T58R3227G07	1	60	CU	0.25	120/208/240/480	48	115	40	10225	NONE	Leads Out
9T58K3229	9T58R3229G07	1	60	CU	0.50	120/208/240/480	48	115	40	12225	NONE	Leads Out
9T58K3533	9T58R3533G07	1	60	CU	0.15	240x480	120/240	55	40	8150	NONE	Leads Out
9T58K3555	9T58R3555G07	1	50	CU	1.50	380/400/416	82/150	100	40	14300	NONE	Leads Out

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K3562	9T58R3562G07	1	60	CU	0.50	240x480	12/24	100	40	10225	NONE	Leads Out
9T58K3932	9T58R3932G07	1	60	CU	0.14	480	277	55	40	6100	NONE	Leads Out
9T58K4083	9T58R4083G07	1	50	CU	0.20	115x230	230/460	80	40	8200	NONE	Leads Out
9T58K4084	9T58R4084G07	1	50	CU	0.30	115/230	43	80	40	10225	NONE	Leads Out
9T58K4170	9T58R4170G07	1	60	CU	0.25	208	115	80	40	8200	NONE	Leads Out
9T58K4175	9T58R4175G07	1	60	CU	1.50	208	82	100	40	14225	NONE	Leads Out
9T58K7781	9T58R7781G07	1	50	CU	0.15	575	120	100	40	8175	NONE	Leads Out
9T58K0047G24	9T58R0047G11	1	60	CU	0.25	230x460	115	80	40	8200	(1) QUARTER-INCH	Screw Terminals
9T58K0067G24	9T58R0067G11	1	50	CU	0.25	230/460/575	115/95	100	40	8250	(1) QUARTER-INCH	Screw Terminals
9T58K2802G24	9T58R2802G11	1	60	CU	0.05	240x480	120/240	55	40	6100	(1) QUARTER-INCH	Screw Terminals
9T58K2803G24	9T58R2803G11	1	60	CU	0.08	240x480	120/240	55	40	6125	(1) QUARTER-INCH	Screw Terminals
9T58K2804G24	9T58R2804G11	1	60	CU	0.10	240x480	120/240	55	40	8100	(1) QUARTER-INCH	Screw Terminals
9T58K2805G24	9T58R2805G11	1	60	CU	0.15	240x480	120/240	55	40	8150	(1) QUARTER-INCH	Screw Terminals
9T58K2806G24	9T58R2806G11	1	60	CU	0.20	240x480	120/240	80	40	8175	(1) QUARTER-INCH	Screw Terminals
9T58K2808G24	9T58R2808G11	1	60	CU	0.30	240x480	120/240	100	40	8200	(1) QUARTER-INCH	Screw Terminals
9T58K2810G24	9T58R2810G11	1	60	CU	0.50	240x480	120/240	100	40	10225	(1) QUARTER-INCH	Screw Terminals
9T58K2824G24	9T58R2824G11	1	60	CU	0.10	600	120/240	55	40	8100	(1) QUARTER-INCH	Screw Terminals
9T58K2826G24	9T58R2826G11	1	60	CU	0.20	600	120/240	80	40	8175	(1) QUARTER-INCH	Screw Terminals
9T58K2874G24	9T58R2874G11	1	60	CU	0.08	120x240	12/24	55	40	6125	(1) QUARTER-INCH	Screw Terminals
9T58K2875G24	9T58R2875G11	1	60	CU	0.10	120x240	12/24	55	40	8100	(1) QUARTER-INCH	Screw Terminals
9T58K3164G24	9T58R3164G11	1	60	CU	0.05	240x480	12/24	55	40	6100	(1) QUARTER-INCH	Screw Terminals
9T58K4052G24	9T58R4052G11	1	60	CU	0.15	208/240	12/24	55	40	8150	(1) QUARTER-INCH	Screw Terminals
9T58K4133G24	9T58R4133G11	1	60	CU	0.15	240x480	12/24	55	40	8150	(1) QUARTER-INCH	Screw Terminals
9T58K0042G42	9T58R0042G21	1	60	CU	0.05	230x460	115	55	40	6100	(1) MIDGET	Screw Terminals
9T58K0043G42	9T58R0043G21	1	60	CU	0.08	240x480	120	55	40	6125	(1) MIDGET	Screw Terminals
9T58K0044G42	9T58R0044G21	1	60	CU	0.10	230x460	115	55	40	8100	(1) MIDGET	Screw Terminals
9T58K0045G42	9T58R0045G21	1	60	CU	0.15	230x460	115	55	40	8150	(1) MIDGET	Screw Terminals
9T58K0046G42	9T58R0046G21	1	60	CU	0.20	230x460	115	80	40	8175	(1) MIDGET	Screw Terminals
9T58K0047G42	9T58R0047G21	1	60	CU	0.25	230x460	115	80	40	8200	(1) MIDGET	Screw Terminals
9T58K0050G42	9T58R0050G21	1	60	CU	0.50	230x460	115	80	40	10225	(1) MIDGET	Screw Terminals
9T58K0082G42	9T58R0082G21	1	50	CU	0.05	208/277/380	115/95	55	40	6150	(1) MIDGET	Screw Terminals
9T58K2805G42	9T58R2805G21	1	60	CU	0.15	240x480	120/240	55	40	8150	(1) MIDGET	Screw Terminals
9T58K2807G42	9T58R2807G21	1	60	CU	0.25	240x480	120/240	80	40	8200	(1) MIDGET	Screw Terminals
9T58K2808G42	9T58R2808G21	1	60	CU	0.30	240x480	120/240	115	40	8200	(1) MIDGET	Screw Terminals
9T58K2873G42	9T58R2873G21	1	60	CU	0.05	120x240	12/24	55	40	6100	(1) MIDGET	Screw Terminals
9T58K2874G42	9T58R2874G21	1	60	CU	0.08	120x240	12/24	55	40	6125	(1) MIDGET	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2875G42	9T58R2875G21	1	60	CU	0.10	120x240	12/24	55	40	8100	(1) MIDGET	Screw Terminals
9T58K2876G42	9T58R2876G21	1	60	CU	0.15	120x240	12/24	55	40	8150	(1) MIDGET	Screw Terminals
9T58K2878G42	9T58R2878G21	1	60	CU	0.25	120x240	12/24	115	40	8200	(1) MIDGET	Screw Terminals
9T58K4145G42	9T58R4145G21	1	50	CU	0.15	230/460/575	115	80	40	8200	(1) MIDGET	Screw Terminals
9T58K4148G42	9T58R4148G21	1	50	CU	0.08	230x460	115	55	40	6150	(1) MIDGET	Screw Terminals
9T58K0043G10	9T58R0043G31	1	60	CU	0.08	240x480	120	55	40	6125	(1) H/K	Screw Terminals
9T58K0047G10	9T58R0047G31	1	60	CU	0.25	230x460	115	80	40	8200	(1) H/K	Screw Terminals
9T58K0050G10	9T58R0050G31	1	60	CU	0.50	230x460	115	80	40	10225	(1) H/K	Screw Terminals
9T58K0052G10	9T58R0052G31	1	60	CU	1.00	230x460	115	80	40	12300	(1) H/K	Screw Terminals
9T58K0054G10	9T58R0054G31	1	60	CU	2.00	240x480	120	100	40	14300	(1) H/K	Screw Terminals
9T58K0070G10	9T58R0070G31	1	50	CU	0.50	230/460/575	115/95	115	40	10225	(1) H/K	Screw Terminals
9T58K0072G10	9T58R0072G31	1	50	CU	1.00	230/460/575	115/95	100	40	14225	(1) H/K	Screw Terminals
9T58K0074G10	9T58R0074G31	1	50	CU	2.00	230/460/575	115/95	100	40	14475	(1) H/K	Screw Terminals
9T58K2804G10	9T58R2804G31	1	60	CU	0.10	240x480	120/240	55	40	8100	(1) H/K	Screw Terminals
9T58K2805G10	9T58R2805G31	1	60	CU	0.15	240x480	120/240	55	40	8150	(1) H/K	Screw Terminals
9T58K2808G10	9T58R2808G31	1	60	CU	0.30	240x480	120/240	100	40	8200	(1) H/K	Screw Terminals
9T58K0044G43	9T58R0044G41	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC	Screw Terminals
9T58K0045G43	9T58R0045G41	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC	Screw Terminals
9T58K0064G43	9T58R0064G41	1	50	CU	0.10	230/460/575	115/95	55	40	8150	(2) CC	Screw Terminals
9T58K0065G43	9T58R0065G41	1	50	CU	0.15	230/460/575	115/95	80	40	8200	(2) CC	Screw Terminals
9T58K0084G43	9T58R0084G41	1	50	CU	0.10	208/277/380	115/95	55	40	8150	(2) CC	Screw Terminals
9T58K0085G43	9T58R0085G41	1	50	CU	0.15	208/277/380	115/95	80	40	8200	(2) CC	Screw Terminals
9T58K3478G43	9T58R3478G41	1	50	CU	0.15	240	24-120	80	40	8175	(2) CC	Screw Terminals
9T58K0042G05	9T58R0042G51	1	60	CU	0.05	230x460	115	55	40	6100	(2) H/K	Screw Terminals
9T58K0044G05	9T58R0044G51	1	60	CU	0.10	230x460	115	55	40	8100	(2) H/K	Screw Terminals
9T58K0045G05	9T58R0045G51	1	60	CU	0.15	230x460	115	55	40	8150	(2) H/K	Screw Terminals
9T58K0048G05	9T58R0048G51	1	60	CU	0.30	230x460	115	80	40	8250	(2) H/K	Screw Terminals
9T58K0064G05	9T58R0064G51	1	50	CU	0.10	230/460/575	115/95	55	40	8150	(2) H/K	Screw Terminals
9T58K2804G05	9T58R2804G51	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) H/K	Screw Terminals
9T58K3019G05	9T58R3019G51	1	60	CU	0.72	120/240/480	82/24	115	40	12225	(2) H/K	Screw Terminals
9T58K1805G05	9T58R1805G57	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) H/K	Leads Out
9T58K1808G05	9T58R1808G57	1	60	CU	0.30	240x480	120/240	100	40	8200	(2) H/K	Leads Out
9T58K0042G48	9T58R0042G61	1	60	CU	0.05	230x460	115	55	40	6100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0043G48	9T58R0043G61	1	60	CU	0.08	240x480	120	55	40	6125	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0044G48	9T58R0044G61	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0045G48	9T58R0045G61	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC + (1) QUARTER-INCH	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0046G48	9T58R0046G61	1	60	CU	0.20	230x460	115	80	40	8175	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0047G48	9T58R0047G61	1	60	CU	0.25	230x460	115	80	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0048G48	9T58R0048G61	1	60	CU	0.30	230x460	115	80	40	8250	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0049G48	9T58R0049G61	1	60	CU	0.38	230x460	115	100	40	8250	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0050G48	9T58R0050G61	1	60	CU	0.50	230x460	115	80	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0051G48	9T58R0051G61	1	60	CU	0.75	230x460	115	80	40	12225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0052G48	9T58R0052G61	1	60	CU	1.00	230x460	115	80	40	12300	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0055G48	9T58R0055G61	1	60	CU	3.00	230x460	115	115	40	14475	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0062G48	9T58R0062G61	1	50	CU	0.05	230/460/575	115/95	55	40	6150	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0064G48	9T58R0064G61	1	50	CU	0.10	230/460/575	115/95	55	40	8150	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0065G48	9T58R0065G61	1	50	CU	0.15	230/460/575	115/95	80	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0066G48	9T58R0066G61	1	50	CU	0.20	230/460/575	115/95	100	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0067G48	9T58R0067G61	1	50	CU	0.25	230/460/575	115/95	100	40	8250	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0068G48	9T58R0068G61	1	50	CU	0.30	230/460/575	115/95	80	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0069G48	9T58R0069G61	1	50	CU	0.38	230/460/575	115/95	80	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0070G48	9T58R0070G61	1	50	CU	0.50	230/460/575	115/95	115	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0072G48	9T58R0072G61	1	50	CU	1.00	230/460/575	115/95	115	40	14225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0082G48	9T58R0082G61	1	50	CU	0.05	208/277/380	115/95	55	40	6150	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0084G48	9T58R0084G61	1	50	CU	0.10	208/277/380	115/95	55	40	8150	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0086G48	9T58R0086G61	1	50	CU	0.20	208/277/380	115/95	100	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0087G48	9T58R0087G61	1	50	CU	0.25	208/277/380	115/95	100	40	8250	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0090G48	9T58R0090G61	1	50	CU	0.50	208/277/380	115/95	115	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0728G48	9T58R0728G61	1	50	CU	0.25	380/415/480	120	100	40	8250	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0945G48	9T58R0945G61	1	50	CU	0.50	380/415/480	120	100	40	12225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2802G48	9T58R2802G61	1	60	CU	0.05	240x480	120/240	55	40	6100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2803G48	9T58R2803G61	1	60	CU	0.08	240x480	120/240	55	40	6125	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2804G48	9T58R2804G61	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2805G48	9T58R2805G61	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2806G48	9T58R2806G61	1	60	CU	0.20	240x480	120/240	80	40	8175	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2807G48	9T58R2807G61	1	60	CU	0.25	240x480	120/240	80	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2808G48	9T58R2808G61	1	60	CU	0.30	240x480	120/240	100	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2809G48	9T58R2809G61	1	60	CU	0.38	240x480	120/240	100	40	8250	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2810G48	9T58R2810G61	1	60	CU	0.50	240x480	120/240	100	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2824G48	9T58R2824G61	1	60	CU	0.10	600	120/240	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2873G48	9T58R2873G61	1	60	CU	0.05	120x240	12/24	55	40	6100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2907G48	9T58R2907G61	1	60	CU	0.10	120x240	120/240	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2913G48	9T58R2913G61	1	60	CU	0.50	120x240	120/240	80	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2930G48	9T58R2930G61	1	50	CU	0.50	240x480	120/240	115	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K3024G48	9T58R3024G61	1	60	CU	0.25	240x480	12/24	80	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K3164G48	9T58R3164G61	1	60	CU	0.05	240x480	12/24	55	40	6100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K4051G48	9T58R4051G61	1	60	CU	0.10	208/240	12/24	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K4132G48	9T58R4132G61	1	60	CU	0.10	240x480	12/24	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0042G38	9T58R0042G71	1	60	CU	0.05	230x460	115	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K0043G38	9T58R0043G71	1	60	CU	0.08	240x480	120	55	40	6125	(2) CC + (1) MIDGET	Screw Terminals
9T58K0044G38	9T58R0044G71	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K0045G38	9T58R0045G71	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K0046G38	9T58R0046G71	1	60	CU	0.20	230x460	115	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K0047G38	9T58R0047G71	1	60	CU	0.25	230x460	115	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K0048G38	9T58R0048G71	1	60	CU	0.30	230x460	115	80	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K0049G38	9T58R0049G71	1	60	CU	0.38	230x460	115	100	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K0050G38	9T58R0050G71	1	60	CU	0.50	230x460	115	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0051G38	9T58R0051G71	1	60	CU	0.75	230x460	115	80	40	12225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0052G38	9T58R0052G71	1	60	CU	1.00	230x460	115	80	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0055G38	9T58R0055G71	1	60	CU	3.00	230x460	115	115	40	14475	(2) CC + (1) MIDGET	Screw Terminals
9T58K0070G38	9T58R0070G71	1	50	CU	0.50	230/460/575	115/95	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0071G38	9T58R0071G71	1	50	CU	0.75	230/460/575	115/95	100	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0072G38	9T58R0072G71	1	50	CU	1.00	230/460/575	115/95	100	40	14225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0073G38	9T58R0073G71	1	50	CU	1.50	230/460/575	115/95	100	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0074G38	9T58R0074G71	1	50	CU	2.00	230/460/575	115/95	100	40	14475	(2) CC + (1) MIDGET	Screw Terminals
9T58K0082G38	9T58R0082G71	1	50	CU	0.05	208/277/380	115/95	55	40	6150	(2) CC + (1) MIDGET	Screw Terminals
9T58K0083G38	9T58R0083G71	1	50	CU	0.08	208/277/380	115/95	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K0084G38	9T58R0084G71	1	50	CU	0.10	208/277/380	115/95	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K0085G38	9T58R0085G71	1	50	CU	0.15	208/277/380	115/95	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K0086G38	9T58R0086G71	1	50	CU	0.20	208/277/380	115/95	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K0087G38	9T58R0087G71	1	50	CU	0.25	208/277/380	115/95	100	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K0088G38	9T58R0088G71	1	50	CU	0.30	208/277/380	115/95	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0089G38	9T58R0089G71	1	50	CU	0.38	208/277/380	115/95	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0090G38	9T58R0090G71	1	50	CU	0.50	208/277/380	115/95	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0091G38	9T58R0091G71	1	50	CU	0.75	208/277/380	115/95	80	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0092G38	9T58R0092G71	1	50	CU	1.00	208/277/380	115/95	100	40	14225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0093G38	9T58R0093G71	1	50	CU	1.50	208/277/380	115/95	100	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0094G38	9T58R0094G71	1	50	CU	2.00	208/277/380	115/95	100	40	14475	(2) CC + (1) MIDGET	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K1945G38	9T58R1945G71	1	60	CU	0.30	575	120	100	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K2802G38	9T58R2802G71	1	60	CU	0.05	240x480	120/240	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2804G38	9T58R2804G71	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2805G38	9T58R2805G71	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K2806G38	9T58R2806G71	1	60	CU	0.20	240x480	120/240	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2807G38	9T58R2807G71	1	60	CU	0.25	240x480	120/240	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2808G38	9T58R2808G71	1	60	CU	0.30	240x480	120/240	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2810G38	9T58R2810G71	1	60	CU	0.50	240x480	120/240	100	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2812G38	9T58R2812G71	1	60	CU	1.00	240x480	120/240	100	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K2813G38	9T58R2813G71	1	60	CU	1.50	240x480	120/240	100	40	14225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2814G38	9T58R2814G71	1	60	CU	2.00	240x480	120/240	115	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K2815G38	9T58R2815G71	1	60	CU	3.00	240x480	120/240	100	40	14475	(2) CC + (1) MIDGET	Screw Terminals
9T58K2824G38	9T58R2824G71	1	60	CU	0.10	600	120/240	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2850G38	9T58R2850G71	1	60	CU	0.05	208/230/460	24-120	55	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2851G38	9T58R2851G71	1	60	CU	0.10	208/230/460	24-120	55	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2852G38	9T58R2852G71	1	60	CU	0.15	208/230/460	24-120	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2853G38	9T58R2853G71	1	60	CU	0.25	208/230/460	24-120	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2854G38	9T58R2854G71	1	60	CU	0.30	208/230/460	24-120	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2855G38	9T58R2855G71	1	60	CU	0.35	208/230/460	24-120	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2856G38	9T58R2856G71	1	60	CU	0.50	208/230/460	24-120	80	40	12225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2873G38	9T58R2873G71	1	60	CU	0.05	120x240	12/24	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2874G38	9T58R2874G71	1	60	CU	0.08	120x240	12/24	55	40	6125	(2) CC + (1) MIDGET	Screw Terminals
9T58K2875G38	9T58R2875G71	1	60	CU	0.10	120x240	12/24	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2876G38	9T58R2876G71	1	60	CU	0.15	120x240	12/24	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K2878G38	9T58R2878G71	1	60	CU	0.25	120x240	12/24	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2879G38	9T58R2879G71	1	60	CU	0.30	120x240	12/24	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2907G38	9T58R2907G71	1	60	CU	0.10	120x240	120/240	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2909G38	9T58R2909G71	1	60	CU	0.20	120x240	120/240	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2911G38	9T58R2911G71	1	60	CU	0.30	120x240	120/240	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2913G38	9T58R2913G71	1	60	CU	0.50	120x240	120/240	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2978G38	9T58R2978G71	1	50	CU	0.50	380/400/416	115/230	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K3024G38	9T58R3024G71	1	60	CU	0.25	240x480	12/24	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K3118G38	9T58R3118G71	1	60	CU	0.05	208	12/24	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K3119G38	9T58R3119G71	1	60	CU	0.08	208	12/24	55	40	6125	(2) CC + (1) MIDGET	Screw Terminals
9T58K3120G38	9T58R3120G71	1	60	CU	0.10	208	12/24	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K3125G38	9T58R3125G71	1	60	CU	0.30	240x480	24	115	40	8200	(2) CC + (1) MIDGET	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K3164G38	9T58R3164G71	1	60	CU	0.05	240x480	12/24	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K4132G38	9T58R4132G71	1	60	CU	0.10	240x480	12/24	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K4133G38	9T58R4133G71	1	60	CU	0.15	240x480	12/24	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K4174G38	9T58R4174G71	1	50	CU	1.50	380/415/480	120	100	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K4194G38	9T58R4194G71	1	60	CU	0.25	208/240/480	24-120	100	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0504G38	9T58R0504G77	1	60	CU	0.15	480	120	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0517G38	9T58R0517G77	1	60	CU	0.30	208	120	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K0534G38	9T58R0534G77	1	60	CU	0.15	600	120	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0537G38	9T58R0537G77	1	60	CU	0.30	600	120	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K0574G38	9T58R0574G77	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0577G38	9T58R0577G77	1	60	CU	0.30	240x480	120/240	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K0702G38	9T58R0702G77	1	60	CU	0.15	480	24	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0944G38	9T58R0944G77	1	60	CU	0.15	208	120	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0953G38	9T58R0953G77	1	50	CU	0.10	380/400/416	110/220	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0957G38	9T58R0957G77	1	50	CU	0.25	380/400/415	110/220	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K1696G38	9T58R1696G77	1	50	CU	0.15	380/400/415	110/220	80	40	8175	(2) CC + (1) MIDGET	Leads Out
9T58K1803G38	9T58R1803G77	1	60	CU	0.08	240x480	120/240	55	40	6125	(2) CC + (1) MIDGET	Leads Out
9T58K1804G38	9T58R1804G77	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) CC + (1) MIDGET	Leads Out
9T58K1806G38	9T58R1806G77	1	60	CU	0.20	240x480	120/240	80	40	8175	(2) CC + (1) MIDGET	Leads Out
9T58K0042G18	9T58R0042G81	1	60	CU	0.05	230x460	115	55	40	6100	(2) CC + (1) H/K	Screw Terminals
9T58K0043G18	9T58R0043G81	1	60	CU	0.08	240x480	120	55	40	6125	(2) CC + (1) H/K	Screw Terminals
9T58K0044G18	9T58R0044G81	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K0045G18	9T58R0045G81	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC + (1) H/K	Screw Terminals
9T58K0046G18	9T58R0046G81	1	60	CU	0.20	230x460	115	80	40	8175	(2) CC + (1) H/K	Screw Terminals
9T58K0047G18	9T58R0047G81	1	60	CU	0.25	230x460	115	80	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K0048G18	9T58R0048G81	1	60	CU	0.30	230x460	115	80	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K0050G18	9T58R0050G81	1	60	CU	0.50	230x460	115	80	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K0062G18	9T58R0062G81	1	50	CU	0.05	230/460/575	115/95	55	40	6150	(2) CC + (1) H/K	Screw Terminals
9T58K0067G18	9T58R0067G81	1	50	CU	0.25	230/460/575	115/95	100	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K0070G18	9T58R0070G81	1	50	CU	0.50	230/460/575	115/95	115	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K0082G18	9T58R0082G81	1	50	CU	0.05	208/277/380	115/95	55	40	6150	(2) CC + (1) H/K	Screw Terminals
9T58K0084G18	9T58R0084G81	1	50	CU	0.10	208/277/380	115/95	55	40	8150	(2) CC + (1) H/K	Screw Terminals
9T58K0087G18	9T58R0087G81	1	50	CU	0.25	208/277/380	115/95	100	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K0090G18	9T58R0090G81	1	50	CU	0.50	208/277/380	115/95	115	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K0091G18	9T58R0091G81	1	50	CU	0.75	208/277/380	115/95	80	40	12300	(2) CC + (1) H/K	Screw Terminals
9T58K0092G18	9T58R0092G81	1	50	CU	1.00	208/277/380	115/95	100	40	14225	(2) CC + (1) H/K	Screw Terminals

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0726G18	9T58R0726G81	1	50	CU	0.10	480	120	80	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K0730G18	9T58R0730G81	1	50	CU	0.30	480	120	100	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K1001G18	9T58R1001G81	1	60	CU	0.20	525	126/145	100	40	8175	(2) CC + (1) H/K	Screw Terminals
9T58K2802G18	9T58R2802G81	1	60	CU	0.05	240x480	120/240	55	40	6100	(2) CC + (1) H/K	Screw Terminals
9T58K2803G18	9T58R2803G81	1	60	CU	0.08	240x480	120/240	55	40	6125	(2) CC + (1) H/K	Screw Terminals
9T58K2804G18	9T58R2804G81	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K2805G18	9T58R2805G81	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) H/K	Screw Terminals
9T58K2806G18	9T58R2806G81	1	60	CU	0.20	240x480	120/240	80	40	8175	(2) CC + (1) H/K	Screw Terminals
9T58K2807G18	9T58R2807G81	1	60	CU	0.25	240x480	120/240	80	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K2808G18	9T58R2808G81	1	60	CU	0.30	240x480	120/240	115	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K2810G18	9T58R2810G81	1	60	CU	0.50	240x480	120/240	100	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K2812G18	9T58R2812G81	1	60	CU	1.00	240x480	120/240	100	40	12300	(2) CC + (1) H/K	Screw Terminals
9T58K2813G18	9T58R2813G81	1	60	CU	1.50	240x480	120/240	100	40	14225	(2) CC + (1) H/K	Screw Terminals
9T58K2824G18	9T58R2824G81	1	60	CU	0.10	600	120/240	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K2830G18	9T58R2830G81	1	60	CU	0.50	600	120/240	80	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K2873G18	9T58R2873G81	1	60	CU	0.05	120x240	12/24	55	40	6100	(2) CC + (1) H/K	Screw Terminals
9T58K2875G18	9T58R2875G81	1	60	CU	0.10	120x240	12/24	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K2930G18	9T58R2930G81	1	50	CU	0.50	240x480	120/240	115	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K3467G18	9T58R3467G81	1	60	CU	0.50	240x480	115	100	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K4174G18	9T58R4174G81	1	50	CU	1.50	380/415/480	120	100	40	14300	(2) CC + (1) H/K	Screw Terminals
9T58K0501G18	9T58R0501G87	1	60	CU	0.06	480	120	55	40	6100	(2) CC + (1) H/K	Leads Out
9T58K0503G18	9T58R0503G87	1	60	CU	0.10	480	120	55	40	8100	(2) CC + (1) H/K	Leads Out
9T58K0504G18	9T58R0504G87	1	60	CU	0.15	480	120	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0507G18	9T58R0507G87	1	60	CU	0.30	480	120	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0511G18	9T58R0511G87	1	60	CU	0.06	208	120	55	40	6100	(2) CC + (1) H/K	Leads Out
9T58K0517G18	9T58R0517G87	1	60	CU	0.30	208	120	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0534G18	9T58R0534G87	1	60	CU	0.15	600	120	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0537G18	9T58R0537G87	1	60	CU	0.30	600	120	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0574G18	9T58R0574G87	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0577G18	9T58R0577G87	1	60	CU	0.30	240x480	120/240	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0702G18	9T58R0702G87	1	60	CU	0.15	480	24	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0705G18	9T58R0705G87	1	60	CU	0.30	480	24	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0944G18	9T58R0944G87	1	60	CU	0.15	208	120	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0954G18	9T58R0954G87	1	50	CU	0.15	380/400/415	110/220	80	40	8175	(2) CC + (1) H/K	Leads Out
9T58K0956G18	9T58R0956G87	1	50	CU	0.25	380/400/416	110/220	80	40	8250	(2) CC + (1) H/K	Leads Out