

ABB's Full UL rated Transfer Switch portfolio

Full NEMA transfer switch offering – September 2019

TruONE



OEM general purpose, industrial & critical

- Open style ATS in standard or delayed transition
- 30-1200A, 200-480V ratings
- 2, 3 or 4 pole applications
- Modular all-in-one design with wide range of features in 3 controller levels

ZTX UPDATED



Small frame residential, commercial & light industrial

- Standard transition
- 30-1200A, 200-480V ratings
- 2, 3, or 4 pole applications
- Enclosed in type 1 or type 3R enclosures

ZTG UPDATED



General purpose commercial & industrial

- Standard or delayed transition for transfer with a timed "off" position
- Ekip connectivity and advanced interface from 30-1200A,
- Extended ratings up to 3000A & 600Vac (2, 3, or 4 pole), and service entrance

ZTS



Business & industrial critical

- Standard, delayed, or closed transition for make-before-break switching
- Extended ratings up to 4000A & 600Vac (2, 3, or 4 pole), and service entrance
- Maintenance bypass available on all frames and transition types

ZTE



Mission, process & healthcare critical

- Specially-designed for critical applications, with built-in PQ metering, enhanced diagnostics, and connectivity
- Full color graphical display
- Standard, delayed, closed transition & bypass up to 4000A & 600Vac (2, 3 or 4 pole)