



AD Plus Lighting Panelboards

Catalog/Selection Guide



imagination at work

AD Plus Lighting Panelboards

Short circuit ratings	35kAIC @ 600Y/347V, 100kAIC @ 480Y/277V (fully rated)
Main bus ratings	Up to 800A UL (600A CSA)
Mains	Breaker or lug
Enclosures	NEMA 3R, 12, 4X (stainless steel)
Dimensions	20" wide x 5 3/4" deep standard, 30" wide available
Mounting	Flush or surface, concealed hardware and hinges standard, door-within-door and front-hinged-to-box options available
Approvals	UL & CSA



AD Plus Lighting Panelboards

600Vac, Factory Assembled – Three-Phase, 3-Wire/4-Wire

1. Select Interior and Main

Main Lug Interiors^{①④}

Use E150 Line Bolt-on Branch Breakers		Single Main Lugs			Subfeed Main Lugs		
Panel Amps Max	Branch Space Required	Interior Catalog Number	List Price, GO-101	Size (inches)	Interior Catalog Number	List Price, GO-101	Size (inches)
125	0-12	ADF3121MB	\$579.00	25.5	ADF3121SB	\$616.00	28.5
	13-18	ADF3181MB	633.00	28.5	ADF3181SB	670.00	34.5
	19-24	ADF3241MB	728.00	31.5	ADF3241SB	764.00	37.5
	25-30	ADF3301MB	821.00	34.5	ADF3301SB	858.00	40.5
	31-36	ADF3361MB	915.00	37.5	ADF3361SB	951.00	46.5
225	37-42	ADF3421MB	1009.00	40.5	ADF3421SB	1046.00	49.5
	0-12	ADF3122MB	648.00	31.5	ADF3122SB	689.00	31.5
	13-18	ADF3182MB	703.00	37.5	ADF3182SB	743.00	37.5
	19-24	ADF3242MB	796.00	40.5	ADF3242SB	836.00	40.5
	25-30	ADF3302MB	890.00	43.5	ADF3302SB	930.00	43.5
400	31-36	ADF3362MB	984.00	49.5	ADF3362SB	1024.00	49.5
	37-42	ADF3422MB	1077.00	52.5	ADF3422SB	1117.00	52.5
	0-12	ADF3124MB	812.00	40.5	ADF3124SB	907.00	46.5
	13-18	ADF3184MB	890.00	46.5	ADF3184SB	985.00	49.5
	19-24	ADF3244MB	976.00	49.5	ADF3244SB	1071.00	52.5
600	25-30	ADF3304MB	1070.00	52.5	ADF3304SB	1164.00	58.5
	31-36	ADF3364MB	1163.00	58.5	ADF3364SB	1258.00	61.5
	37-42	ADF3424MB	1256.00	61.5	ADF3424SB	1351.00	64.5
	0-12	ADF3126MB	953.00	46.5	—	—	—
	13-18	ADF3186MB	1033.00	49.5	—	—	—
800 ^②	19-24	ADF3246MB	1120.00	52.5	—	—	—
	25-30	ADF3306MB	1214.00	58.5	—	—	—
	31-36	ADF3366MB	1308.00	61.5	—	—	—
	37-42	ADF3426MB	1401.00	64.5	—	—	—
	0-12	ADF3128MB	1350.00	55.5	—	—	—
800 ^②	13-18	ADF3188MB	1545.00	55.5	—	—	—
	19-24	ADF3248MB	1740.00	55.5	—	—	—
	25-30	ADF3308MB	1935.00	55.5	—	—	—
	31-36	ADF3368MB	2130.00	61.5	—	—	—
	37-42	ADF3428MB	2325.00	64.5	—	—	—

Service Information:
 3-ph, 4w 120/208Vac
 3-ph, 3w 480Vac
 3-ph, 4w 480Y/277Vac
 3-ph, 3w 600Vac
 3-ph, 4w 600Y/347Vac
 UL Listed
 CSA Certified

Mains:
 150A - THED, SE
 225A - TFJ, SF
 400A - TJJ, SG
 600A - SG
 800A - SK (UL only)
 150-800A MLO

Branch Breakers:
 15-100A 1P, 2P;
 15-150A 3P
 220A max. double branch
 (100A/120A)

Main Breaker Interiors^{①④}

Use E150 Line Bolt-on Branch Breakers		Interrupting Rating																			
Panel Amps Max.	Branch Space Required	25kA 480Vac ^③				35kA 480Vac				65kA 480Vac				100kA 480Vac				35kA 600Y/347Vac			
		Interior Catalog Number	List Price, GO-101	Sizing Dim's (ln's)	Interior Catalog Number	List Price, GO-101	Sizing Dim's (ln's)	Interior Catalog Number	List Price, GO-101	Sizing Dim's (ln's)	Interior Catalog Number	List Price, GO-101	Sizing Dim's (ln's)	Interior Catalog Number	List Price, GO-101	Sizing Dim's (ln's)	Interior Catalog Number	List Price, GO-101	Sizing Dim's (ln's)		
150	0-12	ADF3121TB	\$974.00	31.5	ADF3121KB	\$1174.00	28.5	ADF3121DB	\$1644.00	28.5	ADF3121GB	\$2160.00	28.5	ADF3121DB	\$1644.00	28.5	ADF3121DB	\$1644.00	28.5		
	13-18	ADF3181TB	1028.00	37.5	ADF3181KB	1228.00	37.5	ADF3181DB	1700.00	31.5	ADF3181GB	2217.00	31.5	ADF3181DB	1700.00	31.5	ADF3181DB	1700.00	31.5		
	19-24	ADF3241TB	1121.00	40.5	ADF3241KB	1321.00	40.5	ADF3241DB	1796.00	34.5	ADF3241GB	2312.00	34.5	ADF3241DB	1796.00	34.5	ADF3241DB	1796.00	34.5		
	25-30	ADF3301TB	1215.00	43.5	ADF3301KB	1415.00	43.5	ADF3301DB	1892.00	37.5	ADF3301GB	2408.00	37.5	ADF3301DB	1892.00	37.5	ADF3301DB	1892.00	37.5		
	31-36	ADF3361TB	1309.00	49.5	ADF3361KB	1509.00	49.5	ADF3361DB	1988.00	40.5	ADF3361GB	2504.00	40.5	ADF3361DB	1988.00	40.5	ADF3361DB	1988.00	40.5		
225	37-42	ADF3421TB	1400.00	52.5	ADF3421KB	1600.00	52.5	ADF3421DB	2084.00	43.5	ADF3421GB	2600.00	43.5	ADF3421DB	2084.00	43.5	ADF3421DB	2084.00	43.5		
	0-12	ADF3122TB	1713.00	43.5	ADF3122KB	923.00	43.5	ADF3122DB	3343.00	43.5	ADF3122GB	3610.00	43.5	ADF3122DB	3343.00	43.5	ADF3122DB	3343.00	43.5		
	13-18	ADF3182TB	1767.00	49.5	ADF3182KB	923.00	49.5	ADF3182DB	3398.00	49.5	ADF3182GB	3664.00	49.5	ADF3182DB	3398.00	49.5	ADF3182DB	3398.00	49.5		
	19-24	ADF3242TB	1859.00	52.5	ADF3242KB	923.00	52.5	ADF3242DB	3493.00	52.5	ADF3242GB	3761.00	52.5	ADF3242DB	3493.00	52.5	ADF3242DB	3493.00	52.5		
	25-30	ADF3302TB	1954.00	55.5	ADF3302KB	923.00	55.5	ADF3302DB	3590.00	55.5	ADF3302GB	3857.00	55.5	ADF3302DB	3590.00	55.5	ADF3302DB	3590.00	55.5		
400	31-36	ADF3362TB	2047.00	61.5	ADF3362KB	923.00	61.5	ADF3362DB	3685.00	61.5	ADF3362GB	3952.00	61.5	ADF3362DB	3685.00	61.5	ADF3362DB	3685.00	61.5		
	37-42	ADF3422TB	2140.00	64.5	ADF3422KB	2785.00	64.5	ADF3422DB	3742.00	64.5	ADF3422GB	4049.00	64.5	ADF3422DB	3742.00	64.5	ADF3422DB	3742.00	64.5		
	0-12	ADF3124TB	2577.00	49.5	ADF3124KB	3410.00	49.5	ADF3124DB	4305.00	49.5	ADF3124GB	4599.00	49.5	ADF3124DB	4305.00	49.5	ADF3124DB	4305.00	49.5		
	0-18	ADF3184TB	2666.00	55.5	ADF3184KB	3499.00	55.5	ADF3184DB	4396.00	55.5	ADF3184GB	4690.00	55.5	ADF3184DB	4396.00	55.5	ADF3184DB	4396.00	55.5		
	19-24	ADF3244TB	2758.00	58.5	ADF3244KB	3591.00	58.5	ADF3244DB	4489.00	58.5	ADF3244GB	4783.00	58.5	ADF3244DB	4489.00	58.5	ADF3244DB	4489.00	58.5		
600	25-30	ADF3304TB	2853.00	61.5	ADF3304KB	3686.00	61.5	ADF3304DB	4584.00	61.5	ADF3304GB	4878.00	61.5	ADF3304DB	4584.00	61.5	ADF3304DB	4584.00	61.5		
	31-36	ADF3364TB	2946.00	67.5	ADF3364KB	3779.00	67.5	ADF3364DB	4680.00	67.5	ADF3364GB	4975.00	67.5	ADF3364DB	4680.00	67.5	ADF3364DB	4680.00	67.5		
	37-42	ADF3424TB	3038.00	70.5	ADF3424KB	3871.00	70.5	ADF3424DB	4775.00	70.5	ADF3424GB	5070.00	70.5	ADF3424DB	4775.00	70.5	ADF3424DB	4775.00	70.5		
	0-12	—	—	—	ADF3126KB	5389.00	49.5	ADF3126DB	6284.00	49.5	—	—	—	ADF3126DB	6284.00	49.5	ADF3126DB	6284.00	49.5		
	0-18	—	—	—	ADF3186KB	5480.00	55.5	ADF3186DB	6375.00	55.5	—	—	—	ADF3186DB	6375.00	55.5	ADF3186DB	6375.00	55.5		
600	19-24	—	—	—	ADF3246KB	5572.00	58.5	ADF3246DB	6467.00	58.5	—	—	—	ADF3246DB	6467.00	58.5	ADF3246DB	6467.00	58.5		
	25-30	—	—	—	ADF3306KB	5666.00	61.5	ADF3306DB	6561.00	61.5	—	—	—	ADF3306DB	6561.00	61.5	ADF3306DB	6561.00	61.5		
	31-36	—	—	—	ADF3366KB	5759.00	67.5	ADF3366DB	6654.00	67.5	—	—	—	ADF3366DB	6654.00	67.5	ADF3366DB	6654.00	67.5		
600	37-42	—	—	—	ADF3426KB	5851.00	70.5	ADF3426DB	6748.00	70.5	—	—	—	ADF3426DB	6748.00	70.5	ADF3426DB	6748.00	70.5		

① Bottom feed supplied as standard. Change last character in catalog number from B to T for top feed.
 ② Box is 30" wide x 7.81" deep.
 ③ TFJ main rated 22,000AIC
 ④ Available up through 78 circuits CSA. Consult Speedi for more information.

For functional pricing only. Use Speedi-Win/Plus for exact quotation and order entry.

AD Plus Lighting Panelboards 600Vac, Factory Assembled

2. Select Branch Breakers

Branch Breakers – E150-Line, Bolt-on

Max. Volts	Frame	Trip	List Price Each, GO-101			Frame	Trip	List Price Each, GO-101			
			Per Circuit					Per Circuit			
			1 pole	2 pole	3 pole			1 pole	2 pole ^③	3 pole	
277V	TED ^{①②}	15-60	\$76.00	—	—	THED ^{①②}	15-30	\$90.00	—	—	
		70-100	175.00	—	—			—	—	—	
480V	TED4 ^{①②}	15-60	—	\$205.00	\$270.00	THED4 ^{①②}	15-60	—	\$263.00	—	
		70-110	—	284.00	338.00			70-110	—	344.00	\$765.00
		125-150	—	—	476.00			125-150	—	—	—
	SEHA ^{①②④}	15-60	—	642.00	747.00	SELA ^{①②④}	15-60	—	661.00	868.00	
		70-100	—	746.00	849.00			70-100	—	856.00	1010.00
		110-150	—	1539.00	1930.00			110-150	—	1920.00	2280.00
600V	TED6 ^{①②}	15-60	—	263.00	302.00	THED6 ^{①②}	15-60	—	—	397.00	
		70-110	—	—	379.00			70-110	—	—	447.00
		125-150	—	—	650.00			125-150	—	—	765.00
	FBV (22 kA)	15-60	156.18	218.12	357.27						
		70-100	256.88	302.18	448.36						
	FBN (25 kA)	15-60	181.79	254.00	415.85						
		70-100	299.00	351.88	521.88						
	FBH (35 kA)	15-60	281.66	383.15	626.95						
		70-100	463.25	530.80	786.80						
	FBL (42 kA) ^⑤	15-60	366.40	511.89	838.05						
		70-100	602.63	709.15	1051.73						

- ① 220A double branch maximum (100/120A, 90/130A, etc.).
- ② Mounting of branch breaker in future space requires hardware kit ASPTED3P, \$83.50
List Price, GO-134B. Provides hardware sufficient to mount (3) 1-pole or (1) 3-pole breaker.
- ③ Requires 3 poles of branch space.
- ④ Spectra branch breakers require barrier ASP25AD65KA.
- ⑤ Max. panel rating is 35kAIC @ 600Y/347V.

Short Circuit Current Ratings (kAIC)

C/B Frame	System Voltages		
	120Y/208V	480Y/277V	600Y/347V
TED	18	18	—
THED	65	25	18
SEHA	65	25	—
SELA	100	65	25
SEPA	100	100	25
FBV	65	35	22
FBN	100	65	25
FBH	100	100	35
TFJ	25	22	18
SFHA	65	35	—
SFLA	100	65	25
SFPA	100	100	25
TJJ	42	25	22
SGHA	42	25	25
SGLA	65	65	35
SGPA	100	100	35

3. Select Subfeed (if required)

Subfeed Breakers – 3 pole maximum

Max. Volts	Frame	Trip	List Price, GO-101	
			2 pole	3 pole
480V	SFHA	175-225	\$1256.00	\$1571.00
	SELA 4	175-225	2297.00	2761.00
600V	TFJ	110-225	855.00	951.00

4. Select Interior Options

Interior Options

Note: Sizing dimensions to be used only for estimating enclosure selection, not to determine interior length.

Options	Description	Catalog Number Option Suffix	125/150A		225A		400A		600A		800A	
			Sizing Adder	List Price Adder, GO-101	Sizing Adder	List Price Adder, GO-101	Sizing Adder	List Price Adder, GO-101	Sizing Adder	List Price Adder, GO-101	Sizing Adder	List Price Adder, GO-101
Optional Lugs ^①	Compression AL	L1	—	\$ 30.00	—	\$ 50.00	—	\$130.00	—	\$175.00	—	—
	Pressure CU	L2	—	49.00	—	49.00	—	92.00	—	114.00	—	—
	Comp. AL Oversize	L3	—	152.00	9"	152.00	—	461.00	—	461.00	—	—
	Press. AL Oversize	L4	—	54.00	9"	54.00	—	330.00	—	330.00	—	—
Subfeed Breaker	2 or 3 Pole TFJ	F1	N/A	—	12"	Price by Device	18"	Price by Device	18"	Price by Device	—	—
Feed Thru	Feed Thru Lugs ^②	T1	9"	164.00	9"	164.00	3"	286.00	6"	286.00	6"	\$451.00
Busbar	600 APSI AL	B1	—	595.00	—	595.00	—	759.00	—	—	—	N/A
	750 APSI AL	B2	—	135.00	—	135.00	—	Std.	—	Std.	—	Std.
	800 APSI CU	B3	—	476.00	—	476.00	—	625.00	—	—	—	N/A
	1000 APSI CU ^③	B4	—	103.00	—	103.00	—	182.00	—	246.00	—	459.00
200% Rated Neutrals ^④	—	N2	—	60.00	—	100.00	—	140.00	—	280.00	N/A	N/A
	—	N3	—	60.00	—	100.00	—	140.00	—	N/A	N/A	N/A

- ① Oversize lugs available on single main lug panels only.
- ② Feed thru lugs not available on subfeed or oversized main lug panels.
- ③ 7 For silver or tin plating 1000 APSI Cu only add \$100 List, GO-101.
- ④ 200% rated neutrals in 600A panels require 30" W box.

AD Plus Lighting Panelboards 600Vac, Factory Assembled

5. Select Box and Front Options (NEMA 1 included as standard)

Front Filler Plates TEDFP1

Field installed

List Price \$1.00 each, GO-101

Standard pack: 50

Box Options

Description	Box Catalog Number Suffix	List Price, GO-101
Blank Endwalls	B	①
Painted Box	P	\$160.00
30" Wide	W	250.00
NEMA 3R/12	3	950.00
Knockout	K	①
NEMA 4X	4S	4950.00

① No charge if included on original order.

Front Options

Description	Front Catalog Number Suffix	List Price, GO-101
Screw Cover	C	\$61.00
Hinged Door-in-Door	D	110.00
Optional Lock: Yale 511S	Y	300.00
Optional Lock: Corbin 15767	L	146.00
Nameplate	N	27.00
Door within a Door①	P	238.00
Stainless Steel Front②	S	1467.00
30" Wide	W	250.00
Screw-on nameplates	U	74.00
Metal directory card holder	M	50.00

① Consists of two lockable doors – one over panel interior and one over box wiring gutters. Yale locks not available.

② Flush only. Available with C and N options.

6. Select TVSS

TVSS Transient Voltage Surge Suppression①

Maximum Surge Current per Mode	Maximum Surge Current per Phase	Description	List Price GO-101
65kA	130kA	TVSS UL1449,UL1283	\$6350.00
80kA	160kA	TVSS UL1449,UL1283	\$7000.00
100kA	200kA	TVSS UL1449,UL1283	\$8500.00
100kA	200kA	TVSS UL1449, no counter	\$2875.00
100kA	200kA	TVSS UL1449	\$3575.00

① For factory installed transient voltage surge suppression (TVSS) units in 10" module, add T6 suffix to interior catalog number and 10" to box height.

7. Accessories

Enclosures①

Sizing Dimensions (Inches)	Box Catalog Number	Inside Box Dim.'s (Inches)			Front Catalog Number
		Length	Width	Depth	
28.5-31.5	AB31	31.5	20	5.81	AF31F,S
34.5-37.5	AB37	37.5	20	5.81	AF37F,S
40.5-43.5	AB43	43.5	20	5.81	AF43F,S
46.5-49.5	AB49	49.5	20	5.81	AF49F,S
52.5-55.5	AB55	55.5	20	5.81	AF55F,S
57.5-64.5	AB64	64.5	20	5.81	AF64F,S
67.5-76.5	AB76	76.5	20	5.81	AF76F,S

Flush fronts are 1.5 inches larger than box. Surface fronts are .25 inches larger than box.

① Box supplied as standard for 225A 150kA and 400A 65 and 100kA ratings is 7.81 inches deep, when used with THLC.

For functional pricing only. Use Speedi-Win/Plus for exact quotation and order entry.

AD Plus Lighting Panelboards

Accessories – Field Installed Kits/Replacement Parts

Enclosures^①

Panel Size	Box Catalog Number	Box Size Inches ^②	List Price ^③ , GO-134B	Front Catalog Number ^④	List Price ^③ , GO-134B
0-25.5	AB25B	25.5	\$166.00	AF25F,S	\$170.00
28.5-31.5	AB31B	31.5	170.00	AF31F,S	174.00
34.5-37.5	AB37B	37.5	182.00	AF37F,S	191.00
40.5-43.5	AB43B	43.5	204.00	AF43F,S	218.00
46.5-49.5	AB49B	49.5	233.00	AF49F,S	257.00
52.5-55.5	AB55B	55.5	261.00	AF55F,S	299.00
57.5-64.5	AB64B	64.5	286.00	AF64F,S	326.00
67.5-76.5	AB76B	76.5	324.00	AF76F,S	367.00

Box Options

Description	Box Catalog Number Suffix ^⑤	List Price, GO-101
7.81 deep ^⑥	D	\$200.00
Painted Box	P	200.00
30" Wide ^⑦	W	250.00
NEMA 3R/12	3	950.00

Front Options

Description	Front Catalog Number Suffix ^⑧	List Price, GO-101
Screw Cover	C	\$61.00
Front hinged to box	D	110.00
Optional Lock: Yale 5116 w/Rosette	Y	300.00
Optional Lock: Corbin 15767	L	146.00
Door within a Door ^⑨	P	238.00
Stainless Steel ^⑩	S	1467.00
30" Wide	W	82.00
Nameplate	N	27.00
Screw-on nameplate	U	74.00
Metal directory	M	50.00

- ① "B" suffix provides blank end walls. Order "K" suffix for endwalls with knockouts.
- ② Standard boxes are 20" wide by 5.81 inches deep.
- ③ Use when ordering items separately for replacement. Do not deduct from panel list price to obtain interior only pricing.
- ④ Flush fronts are 11/2" larger than box. Surface fronts are 1/4" larger.
- ⑤ Add to base box catalog number.
- ⑥ K frame main only.
- ⑦ Includes field installable gutter barrier.
- ⑧ Add to base front catalog number.
- ⑨ Consists of two lockable doors – one over panel interior and one over box wiring gutters. Yale locks not available.
- ⑩ Flush only. Available with C and N options.

Box Extensions

Bolts to box with or without endwall in place. Extensions can be combined.

Box Width and Depth	Box Mounting	Box Extension Length (Inches)	Box Extension Catalog Number	List Price, GO-101		
20 x 5.81	Flush	9	ABX2509F	\$145.00		
		18	ABX2518F	167.00		
		24	ABX2524F	194.00		
	Surface	9	ABX2509S	145.00		
		18	ABX2518S	167.00		
		24	ABX2524S	194.00		
		31	ABX2531S	220.00		
		37	ABX2537S	240.00		
		43	ABX2543S	271.00		
		49	ABX2549S	311.00		
		55	ABX2555S	358.00		
		64	ABX2564S	353.00		
20 x 7.81	Flush	18	ABX2718F	184.00		
		24	ABX2724F	206.00		
	Surface	18	ABX2718S	184.00		
		24	ABX2724S	206.00		
		30 x 5.81	Flush	18	ABX3518F	194.00
				24	ABX3524F	223.00
Surface	18		ABX3518S	194.00		
	24		ABX3524S	223.00		
30 x 7.81	Flush	18	ABX3718F	223.00		
		24	ABX3724F	250.00		
	Surface	18	ABX3718S	223.00		
		24	ABX3724S	250.00		

Box Extensions Covers Only – 10 covers per kit

Description	Catalog Number	List Price, GO-101
9" Covers Surface	ASPABX09S	\$145.00
9" Covers Flush	ASPABX09F	155.00
18" Covers Surface	ASPABX18S	285.00
18" Covers Flush	ASPABX18F	300.00

AD Plus Lighting Panelboards

Accessories – Field Installed Kits/Replacement Parts (continued)

Filler Plates

Breaker Type	Catalog Number	List Price
THQB, THHQB, THQL, THHQL, TEY	TQLFP1	\$2.50 (GO-137A)
TQD, THQD, TED4	TEDFP1	1.00 (GO-101)

Breaker Mounting Hardware Kits

Use to mount breaker in existing space.

Breaker Type	Catalog Number	List Price, GO-134B
TED, THED4	ASPTED3P	\$83.50
TQD, THQD	ASPTQD3P	83.50

Endwall Kits

1 each, field installed, for standard 20"W x 5.81"D boxes.

Description	Catalog Number	List Price, GO-134B
Blank	ABEW2	\$31.00
Knockout	ASKEW2	21.00

Panelboard Parts

Description	Catalog Number	List Price, GO-101
Directory Card	139C5612P1	\$ 2.00
Replacement Panel Lock	569B737P1	22.00
Additional Keys for Above Lock	569B737P5	2.00
Circuit Numbering Strips 1-48	569B806G1	4.00
Circuit Numbering Strips 49-84	569B806G2	4.00
Circuit Numbering Strips 85-120	569B806G3	4.00
Adhesive Backed Lamicoid Nameplate 1 in. x 3 in.	315A7190P1	27.00
Metal Directory Card Holder	139C5491G1	50.00
Directory Card Holder	139C5491P4	10.00
Screw and Clip Kit to Convert Up to 12 Poles of Old Style THQB Breakers to Captive Screw Construction	139C5703G20	5.00
Delta Hi-leg Conversion Kit to Add B-Phase to Plug on AL Panels	APHBL	60.00
Delta Hi-leg Conversion Kit to Add B-Phase to Bolt on AE/AQ Panels	APHBQ	60.00
NEMA 3R/12 Tamper Proof Tork Screw Kit	NEMATRX	30.00
2P to 3P TQD Conv. Kit	ASP2PTQD3P	100.00
2P to 3P TFJ Conv. Kit for horizontal subfeed	ASP2PTFJ3P	100.00
125/225A MLO Dual Lug Kit	ASPFT225	100.00
Barrier Kit [Ⓢ]	ASP25AD65KA	100.00
Service Entrance Kit	ASPSERENT	50.00

Ⓢ Included in factory assembled panels. Panels retrofitted with Spectra branch breakers require barrier kit.

Permanent Circuit Number Kits

Description	Catalog Number	List Price, GO-134B
Numbers 1-48	APN48AD	\$116.00
Numbers 49-84	APN84AD	116.00

Prices and data are subject to change without notice. Should further information be desired, or should particular problems arise that are not sufficiently covered here for the purchaser's purposes, the matter should be referred to the General Electric Company.

General Electric Company
41 Woodford Avenue, Plainville, CT 06062
www.GEindustrial.com
© 2005 General Electric Company



imagination at work