



Controls2GO

GE's 300/400-Line combination enclosed starters are now available through Controls2GO!

With Controls2GO, orders ship from our Mt. Juliet, TN warehouse just 2 business days after you place your order.

Much more than a warehouse, Mt. Juliet is a UL 508 certified panel facility with the capability to provide assembly, modification and functional testing of up to 80% of GE's most popular products.



Combination Enclosed Starters Basic Configurations with 1 NC thermal overload relay

NEMA Type	NEMA Size	Product Number			
		Disconnect Switch	Thermal-Mag CB	Mag Break CB	Accessories
1	1	CR308CT041A1AAAAA	CR307CT04TE1AAAAA	CR387CT04MC1AAAAA	None
		CR308CT941A1AALJA	CR307CT94TE1AALJA	CR387CT94MC1AALJA	CPT, HOA, Red Light
	2	CR308DT041A1AAAAA	CR307DT04TG1AAAAA	CR387DT04MF1AAAAA	None
		CR308DT941A1AALJA	CR307DT94TG1AALJA	CR387DT94MF1AALJA	CPT, HOA, Red Light
	3	CR408E1041A1AAAAA	CR407E104TL1AAAAA	CR487E104MH1AAAAA	None
		CR408E1941A1AALJA	CR407E194TL1AALJA	CR487E194MH1AALJA	CPT, HOA, Red Light
	4	CR408F1041A1AAAAA	CR407F104TQ1AAAAA	CR487F104MN1AAAAA	None
		CR408F1941A1AALJA	CR407F194TQ1AALJA	CR487F194MN1AALJA	CPT, HOA, Red Light

Controls2GO Available Options - Combination Enclosed Starters

Combination Enclosed Starter Features:

- UL Listed, rugged Type 1, 12/3R, 4/4X enclosures
- Door-mounted weather protected NEMA type 4X rated selector switches, pushbuttons and indicating lights for dependable operation
- 100KA short circuit rating available
- Tough electrocoated acrylic primer and polyester powder paint finish to provide protection in the harshest outdoor environments.



Tables represent options for potential configurations. Contact your GE Distributor to validate your selection.

Product Line	
CR308	FVNR Disconnect Switch Size 0-2 (Standard Size Type 1 Enc. Only)
CR307	FVNR Thermal-Mag Circuit Breaker Size 0-2 (Standard Size Type 1 Enc. Only)
CR387	FVNR Mag Break Circuit Breaker Size 0-2 (Standard Size Type 1 Enc. Only)
CR408	FVNR Disconnect Switch Type 1/12/3R/4X Size 0-4 Standard Enclosures
CR407	FVNR Thermal-Mag Circuit Breaker Type 1/12/3R/4X Size 0-4 Standard Enclosures
CR487	FVNR Mag Break Circuit Breaker Type 1/12/3R/4X Size 0-4 Standard Enclosures

NEMA Size	
0, 1, 2, 3, 4	

Enclosure Type ¹	
CR308, CR307, CR387, CR408, CR407, CR487	NEMA Type 1 Standard Size
CR408, CR407, CR487	NEMA Type 12 Standard Size NEMA Type 3R Standard Size NEMA Type 4X Standard Size

¹CR308, CR307, CR387 are hard-tooled construction and CR408, CR407, CR487 are welded construction.

Control Circuit Voltage and CPT	
120V no CPT, Control Fuses	
240V no CPT, Control Fuses	
480V no CPT, Control Fuses	
600V no CPT, Control Fuses	
208V no CPT, Control Fuses	
24V no CPT	
240/120V w/CPT (w/wo + 100VA)	
480/120V w/CPT (w/wo + 100VA)	
600/120V w/CPT (w/wo + 100VA)	
208/120V w/CPT (w/wo + 100VA)	
240/24V w/CPT (w/wo + 100VA)	
480/24V w/CPT (w/wo + 100VA)	
600/24V w/CPT (w/wo + 100VA)	
208/24V w/CPT (w/wo + 100VA)	

Protective Device	
Non Fused Disconnect	

Fuse Clip Rating - Class J (CR308, CR408 only)					
Size					
0	1	2	3	4	
30	30	60	100	200	
	60	100	200	400	

Fuse Clip Rating - Class R (CR308, CR408 only)					
Size					
0	1	2	3	4	
30	30	30	60	100	
	60	60	100	200	
			200		

Fuse Clip Rating - Class J (CR308, CR408 only)					
Size					
0	1	2	3	4	
30	30	30	60	100	
	60	60	100	200	
			200		

Circuit Breaker Rating - Thermal Mag Only (CR307, CR407)					
Size					
0	1	2	3	4	
15	15	30	50	100	
20	20	40	60	125	
	25	50	70	150	
	30	60	80	175	
	40	70	90	200	
			100		
			110		
			125		

Circuit Breaker Rating - Mag Break (CR387, CR487)					
Size					
0	1	2	3	4	
3	15	25	40	80	
7	20	30	50	90	
15	25	40	60	100	
	30	50	70	125	
	40	60	80	150	
			90	175	
			100		

Thermal Overload Relay	
Standard (1NC)	
Standard (1NO-1NC)	
Ambient Compensated (1NC)	
Ambient Compensated (1NO-1NC)	

Solid-State Overload Relay				
Size				
0 & 1	2	3	4	
0.4 - 0.85	6.5 - 13.5	17 - 35	17 - 35	
0.8 - 1.7	13 - 27	35 - 70	35 - 70	
1.6 - 3.4	25 - 50	65 - 135	65 - 135	
3.2 - 6.8				
6.5 - 13.5				
13 - 27				

Auxiliary Contacts	
None	3NO
1NO	3NC
1NC	4NO
1NO-1NC	4NC
2NO	2NO-2NC
2NC	3NO-1NC
2NO-1NC	1NO-3NC
1NO-2NC	

Heavy Duty Pushbutton & Selector Switch Options	
Start (Black) / Stop (Red) Pushbutton	
Hand-Off-Auto (HOA) Selector Switch	
Off-On Selector Switch	
Hand-Off-Auto (HOA) Selector Switch & Start (Black) Pushbutton	
Keyed Hand-Off-Auto (HOA) Selector Switch, Key Removal Center Pos.	

Pilot Light Options: Standard, LED, Push-to-Test	
Red - Across Coil	
Green - Across Coil	
Red - Through NO Aux Contact	
Green - Through NC Aux Contact	
Red - Through NO Aux Contact & Green - Through NC Aux Contact	
Red - Across Coil & Green - Through NC Aux Contact	
Red - Across Coil & Green - Through NC Aux Contact & Unwired Amber	

HP & Voltage Ratings to NEMA Size				
Hp Rating	NEMA Size			
	208V	240V	480V	600V
1	0	0	0	0
2	0	0	0	0
3	0	0	0	0
5	1	1	0	0
7 1/2	1	1	1	1
10	2	2	1	1
15	3	2	2	2
20	3	3	2	2
25	3	3	2	2
30	4	3	3	3
40	4	4	3	3
50		4	3	3
60			4	4
75			4	4
100			4	4

Amp Ratings to NEMA Size	
Max Amps	NEMA Size
18	0
27	1
45	2
90	3
135	4

For more detailed product information visit www.geindustrial.com/GE2GO



Authorized GE Distributors: Please refer to our new Product Configurators on EliteNet.

