



GE Consumer & Industrial -
Electrical Distribution

Current Rating
60 Amperes

Voltage Rating
2-pole - 120/240 Vac

Frequency Rating
50/60 Hertz

Molded Case Circuit Breakers Q Line

Type THQB/THHQB - Model C
Long-time Delay and Instantaneous
Time-current Curves

Curves show circuit breaker in open air, 40°C
ambient, wired with conductors of
corresponding rating, no prior load. For all other
ambients, use rating shift index at top of sheet.

DES-065 Supersedes GES-6203A

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.