



GE Industrial Solutions

480V Max  
50/60 Hz  
For Sensors and Setting information see table at upper right

### Molded Case Circuit Breaker Record Plus™ Type FE Current Limiting with PremEon™ S Adjustable Solid-State Trip

Long-Time, and Instantaneous  
with Tracking Short-Time  
Time-Current Curves

## DES-115

#### Adjustments

Adjustable Long Time(LT) Pickup  
Adjustable Instantaneous pick-up settings in multiples of CT sensor rating:  
2, 3, 4, 5, 6, 7, 8, 9.5, 11.5, 13.5

**Note 1:** Operation above 60Hz and 50C may require thermal and interrupting derating of the circuit breaker. Refer to Selection and Application manual.