



GE Industrial Solutions

600V Max
50/60 Hz
For Sensors and Setting information see table at upper right

Molded Case Circuit Breaker Record Plus™ Type FG Current Limiting with PremEon™ S Adjustable Solid-State Trip

Long-Time, and Instantaneous with Tracking Short-Time Time-Current Curves

DES-118

Adjustments

Adjustable Long Time(LT) Pickup
Adjustable Instantaneous pick-up settings in multiples of CT sensor rating:
FG 250A and 400A: 2, 3, 4, 5, 6, 7, 8, 9.5, 11.5, 13.5
FG 600A: 2, 3, 4, 5, 6, 7, 8, 9, 10, 11

Note 1: Operation above 60Hz and 50C may require thermal and interrupting derating of the circuit breaker. Refer to Selection and Application manual.