



GE Industrial Solutions

Current Ratings

Frame Amperes	CT Sensor Amperes
600	250, 400, 600

Voltage Ratings

600 Vac max.
50/60 Hz

**MAG-BREAK™ Motor Circuit Protector
Record Plus™ Type FG
with PremEon™ S Adjustable Solid-State Trip**

Instantaneous
with Tracking Short-Time delay
Time-Current Curves

DES-120

Instantaneous pickup settings in multiples of CT sensor rating:
FG 250A and 400A: 2, 3, 4, 5, 6, 7, 8, 9.5, 11.5, 13.5
FG 600A: 2, 3, 4, 5, 6, 7, 8, 9, 10, 11