


MULTIPLE OF CURRENT SENSOR AMPERES



GE Energy Industrial Solutions

Available Ratings (Amperes)

Type	Model	Frame	Current Sensor (S)	Rating Plug
MCCB	SK	1200	800	300, 350, 400, 450, 500, 600, 700, 750, 800
			1200	450, 500, 600, 700, 750, 800, 900, 1000, 1100, 1200

Voltage Rating: 600Vac, 50 to 60 Hz systems

Notes:

- Do not use on other than 50 and 60Hz systems
- 450A and 1000A rating plugs available on 100% rated 1000A max. SK breakers

Molded Case Circuit Breaker

Type SK with *micro*EntelliGuard™ Trip Unit Time Current Curves

Instantaneous & Reduced Energy Let-through Instantaneous (RELT) Settings

Curves apply at 50 to 60 Hertz and from -20°C to 55°C breaker ambient temperature

DES-217D

Programmer Adjustments

Instantaneous Function:

Pickup Settings: 2.0 to 10.0 in increments of 0.5 multiples of current sensor amps (X)

RELT Function:

Pickup Settings: 1.5 to 10.0 in increments of 0.5 multiples of current sensor amps (X)