



The Time Current Curves below have been superseded. Please see Time-Current Curve DES-207 for *all* UL SMR1 Solid State Trip FG600 Breakers.

- ~~DES-072~~
- ~~DES-073~~
- ~~DES-042~~
- ~~DES-043~~
- ~~DES-044~~
- ~~DES-045~~
- ~~DES-046~~
- ~~DES-047~~
- ~~DES-048~~
- ~~DES-049~~
- ~~DES-050~~
- ~~DES-051~~
- ~~DES-052~~
- ~~DES-053~~
- ~~DES-054~~
- ~~DES-055~~
- ~~DES-056~~
- ~~DES-056~~
- ~~DES-057~~
- ~~DES-058~~
- ~~DES-059~~
- ~~DES-060~~

**DES-207**

Available Three Phase Symmetrical Short Circuit Current (KILOAMPS) See DES-040, DES-041

100A Rating Plug  
Inst set at 11x In

Maximum total clear time.



Case Circuit Breaker

SMR1 Solid State Trip Plus™ Type FG, 600A Frame

Plug: FGRP3K0100

Adjustable Instantaneous (In) 500-2750A

In = Sensor Rating In Amps

Inst = Breaker Grid Position

Interruption ratings per DEA-382